



EC-26368-000

SHT 1.1


NOTE:

- 1 A POSITIVE GOING VOLTAGE AT TERMINAL 2, RELATIVE TO TERMINAL 1, CAUSES A DECREASE IN PRESSURE AT THE SOUND OUTLET.
- 2 LOCATED FROM TWO SURFACES FOR CUSTOMER CONVENIENCE. ONLY APPLICABLE FROM ONE SURFACE, NOT TO BE USED TOGETHER.



SCALE 2:1
NOMINAL WEIGHT
.42 GRAMS

DIMENSIONS IN MILLIMETERS [INCHES]



0,64 [.025]
MAXIMUM
SOLDER BUILDUP

Revision	C.O. #	Implementation Date	RELEASE LEVEL	REVISION
C	CI0115009	8-1-13	Active	C
B	CI0106330	9-3-07		
A	CI0103430	11-18-05		

SCALE: 4:1

DO NOT SCALE DRAWING

TITLE: RECEIVER

OUTLINE DRAWING

EC-26368-000


SHT 1.1

DR. BY	DATE
CRG	11-18-05
CK. BY	DATE
GJP	11-22-05
APP. BY	DATE
GJP	11-22-05

KE111ASIZE.FRM

Rev: B

KNOWLES ELECTRONICS
ITASCA, ILLINOIS U.S.A.



NOTES:

1. MEASUREMENTS MADE USING 10mm (.394") OF 1mm (.039") ID TUBE CONNECTED TO A SIMULATED ANSI S3.7 TYPE HA-3 COUPLER . (IEC 60318-5).
2. SENSITIVITY
- | FREQUENCY | MIN. | MAX. |
|-----------|-------|-------|
| 200 | 99.0 | 105.0 |
| 500 | 101.0 | 107.0 |
| 1000 | 105.0 | 111.0 |
| 1300-2000 | 116.0 | 122.0 |
| 2300-2900 | 105.0 | --- |
| 2900-3900 | 109.0 | 115.0 |
3. RESPONSE, IMPEDANCE, AND DISTORTION MEASUREMENTS MADE USING THE ELECTRICAL TEST CONDITIONS SHOWN BELOW.
4. ELECTRICAL SOURCE IMPEDANCE MUST BE GREATER THAN 20 TIMES 1KHz IMPEDANCE FOR TEST CONDITIONS SHOWN BELOW.
5. INDIVIDUAL SPECIFICATIONS:

PORT LOCATION	IMPEDANCE OHMS ±15%		DCR @20°C OHMS ±10%	DISTORTION		ELECTRICAL TEST CONDITIONS	
	1KHz	500Hz		MAX. %	FREQ Hz	AC mA RMS	DC mA
12S	100	54	26.3	10	800	2.19	0

Revision	C.O. #	Implementation Date	RELEASE LEVEL		REVISION
C	C10115009	8-1-13	Active		C
B	C10106330	9-3-07			
A	C10103430	11-18-05			
TITLE:			RECEIVER		DR. BY DATE
			PERFORMANCE SPECIFICATION		CRG 11-18-05
			EC-26368-000		CK. BY DATE
			SHT 2.1		GJP 11-22-05
					APP. BY DATE
					GJP 11-22-05

KNOWLES ELECTRONICS
ITASCA, ILLINOIS U.S.A.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Knowles:](#)

[EC-26368-000](#)