


REVISIONS				DATE	APPD
0	PRODUCT RELEASE	3/21/86	RB	RB	RB
A	REVISED PER 0430-0364-97	9/24/97	RB	RB	RB



- △ FINISH: 1.27µm [0.00050] MIN THICK NICKEL PLATE ALL OVER. 0.76µm [0.00030] MIN THICK GOLD PLATE OVER NICKEL IN CONTACT AREA AND 2.54µm [0.00100] MIN THICK TIN-LEAD PLATE OVER NICKEL ON SOLDERLEAD.
- △ THIS REQUIREMENT IS BASED ON A 0.82 [0.032] MAXIMUM EFFECTIVE DIAMETER (DIAGONAL) OF THE SOLDERLEADS.
- △ FINISH: 1.27µm [0.00050] MIN THICK TIN PLATE.


79.451 [3.128]	78.23-78.40 [3.080-3.090]	55	64.465 [2.538]	63.25-63.50 [2.490-2.500]	43	146.46 [5.766]	78.64-78.65 [3.092-3.095]	63.55-63.70 [2.502-2.508]	63.627 [2.505]	4.70-4.95 [1.85-1.95]	2.92-3.43 [1.15-1.35]	100	145244-1
RC	RB	RA	LC	LB	LA	W	V	U	T	S	L	NO. OF DUAL POSN	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm (INCHES) TOLERANCES ON: 2 PLC DEC ± .13 (1.005) 3 PLC DEC ± .13 (1.005) ANGLES RATERIAL	DR 3/21/86 R BROWN CHK 3/21/86 R BENDORF APPD 3/21/86 R BENDORF PRODUCT SPEC	AMP AMP Incorporated Harrisburg, PA 17105-3608
FINISH	APPLICATION SPEC	NAME
WEIGHT	SCALE	SIZE
	4:1	CARE CODE
		DRAWING NO
		C=145244
		SHEET
		1 OF 2

CUSTOMER DRAWING



DETAIL H
SCALE 10:1



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm (INCHES) TOLERANCES ON + 2 P.L.C DEC ± .13 (1.005) 3 P.L.C DEC ± .3 ANGLES MATERIAL		DR 3/21/96 S BOND CHK 3/21/96 R BENDORF APRD 3/21/96 R BENDORF APRD 3/21/96 O SARKER PRODUCT SPEC APPLICATION SPEC	NAME	 AMP Incorporated Harrisburg, PA 17105-3600 CONNECTOR ASSEMBLY, DUAL POSN, HIGH SPEED, STANDARD EDGE	
FINISH		SIZE	CASE CODE	DRAWING NO	
-		D	00779	C -145244	
WEIGHT		SCALE	4:1	SHEET	2 OF 2

CUSTOMER DRAWING