




THIS DOCUMENT IS THE PROPERTY OF  
KEYSTONE ELECTRONICS CORP. AND  
SHALL NOT BE REPRODUCED, DISTRIBUTED  
OR USED AS A BASIS FOR MANUFACTURE  
WITHOUT PRIOR WRITTEN PERMISSION  
FROM KEYSTONE ELECTRONICS CORP.

# PC BOARD PATTERN



## ACTUAL SIZE



NOTE:

## TAPE AND REEL SPECIFICATIONS:

1. TAPE:  
MAT'L - ALL CONDUCTIVE POLYSTYRENE CARRIER  
ANSI/EIA-481 STANDARD
2. REEL:  
7.00 [178.0] DIA. , 1000 PIECES PER REEL

## JUMPER SPECIFICATIONS:

1. MAT'L- .028 [0.70] TH'K COPPER  
FINISH- SILVER PLATE

|          |                          |      |
|----------|--------------------------|------|
| 10.01.15 | CHANGE AS PER ECN 15-109 | B    |
| 8.18.14  | CHANGE AS PER ECN 14-085 | A    |
| DATE     | DESCRIPTION              | REV. |

| KEYSTONE ELECTRONICS CORP.                                      |  |         |         |
|-----------------------------------------------------------------|--|---------|---------|
| www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900 |  |         |         |
| PART NAME                                                       |  |         |         |
| 0603 JUMPER ON TAPE AND REEL                                    |  |         |         |
| MATERIAL                                                        |  |         |         |
| AS NOTED                                                        |  |         |         |
| FINISH                                                          |  | DRN BY  | DATE    |
| AS NOTED                                                        |  | NT      | 8.01.14 |
| TOLERANCES                                                      |  | APP'D   | SCALE   |
| INCH [MM]                                                       |  | LN      | 1X, 30X |
| DECIMAL ±.005 [±0.13]                                           |  | DWG NO. |         |
| ANGULAR ± 1°                                                    |  | 5110    |         |
| UNLESS OTHERWISE SPECIFIED                                      |  | C       |         |