

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	U1	REVISED PER ECO-11-004917	11MAR11	RK	HMR
	U2	REVISED PER ECO-17-006294	09OCT2017	RS	DR

1

FOR $\varnothing$ 12.700 [$\varnothing$.500] MAX WIRE INSULATION.

2


MATERIAL: BODY; COPPER PER ASTM B152
INSULATION; PVC
COLOR; GREEN


3


FINISH: BODY; TIN PLATE PER ASTM B-545

AMP WIRE RANGE	 Listed	 LR7189 Certified
18-8 AWG SOLID OR STRANDED	18-8 AWG SOLID OR STRANDED	18-8 AWG SOLID OR STRANDED

STAMPING DETAIL







INSULATION

BODY

250	LOOSE PIECE	320788
QTY	DESCRIPTION	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111


FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.127[.005]

4 PLC ± -

ANGLES ± -

FINISH

MATERIAL

2

DWN
G KRUPER
1/93

CHK
R HERSEY
1/93

APVD
M ELLIS
1/93

PRODUCT SPEC
UL 486C

APPLICATION SPEC
114-2149

WEIGHT
-

CUSTOMER DRAWING

 TE Connectivity

NAME
SPLICE, WIRE, CLOSED END
18-8 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-320788

RESTRICTED TO
-

SCALE
2:1

SHEET
1 OF 1

REV
U2

1470-19 (1/15)