


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO. SPC-F005	Effective: 12/21/98			DCP No. 480
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKED	DATE	APPRVD	DATE
809	A	RELEASED	DJC	8/20/99	JJC	2/29/00	JWM	3/1/00



SPECIFICATIONS:

- MATERIAL:
- CONNECTOR:
- HOUSING: THERMOPLASTIC, GLASS FIBER FILL, UL94V-0
- CONTACT: PHOSPHOR BRONZE, GOLD PLATING ON CONTACT INTERFACE
- SHELL: STEEL, TIN-LEAD PLATING OVER COPPER UNDERPLATING
- CABLE: USB STANDARD FULL SPEED TYPE, UL94V-0
- OVERMOLD: PVC, UL94V-0
- ELECTRICAL:
- VOLTAGE: 30 V AC
- CURRENT: 1A MAXIMUM PER CONTACT
- MECHANICAL:
- RANDOM VIBRATION: NO DISCONTINUITY OF 1uS OR LONGER DURATION
- PHYSICAL SHOCK: NO DISCONTINUITY OF 1uS OR LONGER DURATION
- INSERTION FORCE: 4KG MAX
- WITHDRAWAL FORCE: 1~4KG
- ENVIRONMENTAL:
- THERMAL SHOCK: 10 CYCLE -55° AND +85°C
- COLOR:
- OFF WHITE

WIRE DIAGRAM

