


AS85049/52 and MS3417 Straight Strain Relief Self-Locking or Non-Self-Locking



CONNECTOR DESIGNATOR:	
A	AS50151 Series AS34001 Crimp, MIL-DTL-26482 Series II, SAE-AS1703 Crimp Series III, MIL-DTL-83723 Series I & III



Superseded PART NUMBER		
MS3417-10 A		
Basic Part No. (Non-Self-Locking)	Dash No.	Metal and Finish Designator
		A = Aluminum 1000 Hour Cadmium Olive Drab over Electroless Nickel C = Aluminum, Cadmium Olive Drab G = Aluminum Black Anodize N = Aluminum, Electroless Nickel

S = Self-Locking
-1 = Non-Self-Locking
N = Non-Detented

Material and Finish Designator
A = Aluminum, Black Anodize
N = Aluminum, Electroless Nickel
W = Aluminum, 1000 Hour Cadmium Olive Drab over Electroless Nickel

- ### APPLICATION NOTES
1. Assembly to be identified with manufacturer's name and part number, space permitting.
 2. Cable Entry is defined as the accommodation entry for the wire bundle or cable.
 3. Dimensions are not intended for inspection criteria.
 4. For complete dimensions, see the applicable Military Specification.
 5. Metric dimensions (mm) are in parentheses.




TABLE I: Shell Size, Cable Entry and Backshell Dimensions											
Dash No.	A Thread Class 2B	Ø E Max Self-Locking		F Max Self-Locking		G Max	Cable Entry				
							Min		Max		
3*+	.562 - 24 UNEF	-	-	-	-	.782 (19.9)	.125 (3.2)	.204 (5.2)			
8	.500 - 20 UNF	.885 (22.5)	.73 (18.5)	.782 (19.9)	.125 (3.2)	.204 (5.2)					
10	.625 - 24 UNEF	1.010 (25.7)	.85 (21.6)	.862 (21.9)	.187 (4.7)	.286 (7.3)					
12	.750 - 20 UNEF	1.135 (28.8)	.98 (24.9)	1.003 (24.6)	.291 (7.4)	.416 (10.6)					
14	.875 - 20 UNEF	1.260 (32.0)	.98 (24.9)	1.061 (25.5)	.351 (8.9)	.476 (12.1)					
16	1.000 - 20 UNEF	1.385 (35.2)	1.10 (27.9)	1.234 (26.9)	.501 (12.7)	.626 (15.9)					
18	1.062 - 18 UNEF	1.510 (38.4)	1.35 (34.3)	1.466 (35.4)	.518 (13.2)	.706 (17.9)					
20	1.188 - 18 UNEF	1.635 (41.5)	1.98 (50.3)	1.572 (37.2)	.581 (14.8)	.831 (21.1)					
22	1.313 - 18 UNEF	1.760 (44.7)	2.73 (69.3)	1.688 (39.9)	.644 (16.4)	.956 (24.3)					
24	1.438 - 18 UNEF	1.885 (47.9)	2.88 (73.2)	1.790 (43.1)	.706 (17.9)	1.081 (27.5)					
28+	1.750 - 18 UNS	2.135 (54.2)	2.528 (64.2)	2.035 (45.5)	.750 (19.1)	1.187 (30.1)					
32+	2.000 - 18 UNS	2.395 (60.8)	2.591 (65.8)	2.386 (51.7)	.875 (22.2)	1.250 (31.8)					
36+	2.250 - 16 UN	2.635 (66.9)	2.13 (54.1)	2.446 (60.6)	.938 (23.8)	1.375 (34.9)					
40+	2.500 - 16 UN	2.885 (73.3)	2.44 (62.0)	2.566 (65.2)	.938 (23.8)	1.500 (38.1)					
44+	2.750 - 16 UN	3.135 (79.6)	3.00 (76.2)	2.860 (72.6)	1.188 (30.2)	1.750 (44.5)					
48+	3.000 - 16 UN	3.385 (86.0)	3.40 (86.4)	3.344 (84.9)	1.312 (33.3)	1.875 (47.6)					
61*+	1.500 - 18 UNEF	-	-	1.775 (45.1)	.706 (17.9)	1.081 (27.5)					

* Not Available in Self Locking + Not Available under M83723/15S