

**DESCRIPTION**

The SG79xxA/SG79xx series of negative regulators offer self-contained, fixed-voltage capability with up to 1.5A of load current and input voltage up to -30V. With a variety of output voltages this regulator series is an optimum complement to the SG7800A/SG7800 positive three terminal regulators.

These units feature a unique band gap reference which allows the SG79xxA series to be specified with an output voltage tolerance of  $\pm 1.5\%$ .

The SG79xxA versions also offer much improved line regulation characteristics. All protective features of thermal shutdown, current limiting, and safe-area

control have been designed into these units and since these regulators require only a single output capacitor (SG79xx series) or a capacitor and 5mA minimum load (SG120 series) for satisfactory performance, ease of application is assured.

Although designed as fixed-voltage regulators, the output voltage can be increased through the use of a simple voltage divider. The low quiescent drain current of the device insures good regulation when this method is used.

These devices are available in hermetically sealed TO-257 (both case grounded 'G' and isolated 'IG'), TO-3, TO-39 and LCC packages.

**IMPORTANT:** For the most current data, consult MICROSEMI's website: <http://www.microsemi.com>


**KEY FEATURES**

- Output Voltage Set Internally to  $\pm 1.5\%$  on SG79xxA
- Output Current to 1.5A
- Excellent Line and Load Regulation
- Foldback Current Limiting
- Thermal Overload Protection
- Voltages Available: -5V, -12V, -15V
- Contact Factory for Other Voltage Options
- Available in Surface Mount Package

**HIGH RELIABILITY FEATURES**

- SG79xxA/SG79xx

- Available to MIL-STD - 883,  $\uparrow$  1.2.1
- MIL-M38510/11501BXA - JAN7905T
- MIL-M38510/11505BYA - JAN7905K
- MIL-M38510/11502BXA - JAN7912T
- MIL-M38510/11506BYA - JAN7912K
- MIL-M38510/11503BXA - JAN7915T
- MIL-M38510/11507BYA - JAN7915K
- MIL-M38510/11508BYA - JAN7924K
- MSC-AMSG level "S" Processing Available
- Available to DSCC
- Standard Microcircuit Drawing (SMD)

**PRODUCT HIGHLIGHT**
**SCHEMATIC DIAGRAM**


**ABSOLUTE MAXIMUM RATINGS**

| Device Output Voltage | Input Voltage | Input Voltage Differential<br>(Output Shorted to Ground) |
|-----------------------|---------------|----------------------------------------------------------|
| -5V                   | -35V          | 35V                                                      |
| -12V                  | -35V          | 35V                                                      |
| -15V                  | -40V          | 35V                                                      |

Operating Junction Temperature .....150°C  
 Storage Temperature Range ..... -65°C to 150°C  
 Lead Temperature (Soldering 10 seconds) .....300°C

Note: Exceeding these ratings could cause damage to the device. All voltages are with respect to Ground. Currents are positive into, negative out of specified terminal.

**THERMAL DATA**
**K TO-3 3-Pin Metal Can**

|                                                       |         |
|-------------------------------------------------------|---------|
| THERMAL RESISTANCE-JUNCTION TO CASE, $\theta_{JC}$    | 3.0°C/W |
| THERMAL RESISTANCE-JUNCTION TO AMBIENT, $\theta_{JA}$ | 35°C/W  |

**T TO-39 3-Pin Metal Can**

|                                                       |         |
|-------------------------------------------------------|---------|
| THERMAL RESISTANCE-JUNCTION TO CASE, $\theta_{JC}$    | 15°C/W  |
| THERMAL RESISTANCE-JUNCTION TO AMBIENT, $\theta_{JA}$ | 120°C/W |

**G TO-257 3-Pin Hermetic**

|                                                       |         |
|-------------------------------------------------------|---------|
| THERMAL RESISTANCE-JUNCTION TO CASE, $\theta_{JC}$    | 3.5°C/W |
| THERMAL RESISTANCE-JUNCTION TO AMBIENT, $\theta_{JA}$ | 42°C/W  |

**IG TO-257 3-Pin Hermetic (Isolated)**





|                                                       |         |
|-------------------------------------------------------|---------|
| THERMAL RESISTANCE-JUNCTION TO CASE, $\theta_{JC}$    | 4.0°C/W |
| THERMAL RESISTANCE-JUNCTION TO AMBIENT, $\theta_{JA}$ | 42°C/W  |

**L Leadless Chip Carrier 20-Pin Ceramic**

|                                                       |         |
|-------------------------------------------------------|---------|
| THERMAL RESISTANCE-JUNCTION TO CASE, $\theta_{JC}$    | 35°C/W  |
| THERMAL RESISTANCE-JUNCTION TO AMBIENT, $\theta_{JA}$ | 120°C/W |

Junction Temperature Calculation:  $T_J = T_A + (P_D \times \theta_{JA})$ .

The  $\theta_{JA}$  numbers are guidelines for the thermal performance of the device/pc-board system. All of the above assume no ambient airflow.

**CHARACTERISTIC CURVES**

**Figure 1 – Maximum Average Power Dissipation**

**Figure 2 – Quiescent Current vs. Load**

**Figure 3 – Temperature Coefficient**

**Figure 4 – Short-circuit Current vs.  $V_{IN}$**



#### CHARACTERISTIC CURVES




Figure 5 – Quiescent Current vs.  $V_{IN}$




Figure 6 – Short-circuit Current vs.  $V_{IN}$




Figure 7 – Dropout Characteristics






Figure 8 – Ripple Rejection vs. Frequency

**APPLICATIONS**

**Figure 9 – Fixed Output Regulator**

- Note:
1. C1 is required only if regulator is separated from rectifier filter.
  2. Both C1 and C2 should be low E.S.R. types such as solid tantalum. If aluminum electrolytic capacitors are used, at least 10 times values shown should be selected.
  3. If large output capacities are used, the regulators must be protected from momentary input shorts. A high current diode.


**Figure 10 – Circuit for Increasing Output Voltage**

- Note: C3 optional for improved transient response and ripple rejection.

$$V_{OUT} = V(\text{REGULATOR}) \frac{R_1 + R_2}{R_1}$$

$$R_2 = \frac{V(\text{REG})}{15\text{mA}}$$

**RECOMMENDED OPERATING CONDITIONS**

| Parameter                                     | SG79xx / 79xxA |     |     | Units |
|-----------------------------------------------|----------------|-----|-----|-------|
|                                               | Min            | Typ | Max |       |
| Operating Junction Temperature Range (Note 2) | -55            |     | 150 | °C    |

Note 2: Range over which the device is functional.

**ELECTRICAL CHARACTERISTICS**

Unless otherwise specified, these specifications apply over the operating ambient temperatures for SG7905A / SG7905 with  $-55^{\circ}\text{C} \leq T_A \leq 125^{\circ}\text{C}$ ,  $V_{\text{IN}} = -10\text{V}$ ,  $I_O = 500\text{mA}$  for the K, G, and IG – Power Packages,  $I_O = 100\text{mA}$  for the T and L packages,  $C_{\text{IN}} = 2\mu\text{F}$ , and  $C_{\text{OUT}} = 1\mu\text{F}$ . Low duty cycle pulse testing techniques are used which maintains junction and case temperatures equal to the ambient temperature.

| Parameter                      | Test Conditions                                                                       | SG7905A |       |       | SG7905 |       |       | Units              |
|--------------------------------|---------------------------------------------------------------------------------------|---------|-------|-------|--------|-------|-------|--------------------|
|                                |                                                                                       | Min     | Typ   | Max   | Min    | Typ   | Max   |                    |
| Output Voltage                 | $T_J = 25^{\circ}\text{C}$                                                            | -4.95   | -5.00 | -5.08 | -4.80  | -5.00 | -5.20 | V                  |
| Line Regulation (Note 1)       | $V_{\text{IN}} = -7.5\text{V to } -25\text{V}$ , $T_J = 25^{\circ}\text{C}$           |         | 5     | 25    |        | 3     | 50    | mV                 |
|                                | $V_{\text{IN}} = -8\text{V to } -12\text{V}$ , $T_J = 25^{\circ}\text{C}$             |         | 3     | 12    |        | 1     | 25    | mV                 |
| Load Regulation (Note 1)       | Power Pkgs: $I_O = 5\text{mA to } 1.5\text{A}$ , $T_J = 25^{\circ}\text{C}$           |         | 15    | 75    |        | 15    | 100   | mV                 |
|                                | $I_O = 250\text{mA to } 750\text{mA}$ , $T_J = 25^{\circ}\text{C}$                    |         | 15    | 25    |        | 15    | 25    | mV                 |
|                                | T – Pkg: $I_O = 5\text{mA to } 500\text{mA}$ , $T_J = 250^{\circ}\text{C}$            |         | 5     | 30    |        | 5     | 100   | mV                 |
| Total Output Voltage Tolerance | $V_{\text{IN}} = -8\text{V to } -20\text{V}$                                          |         |       |       |        |       |       |                    |
|                                | Power Pkgs: $I_O = 5\text{mA to } 1.0\text{A}$ , $P \leq 20\text{W}$                  | -4.85   | -5.00 | -5.15 | -4.70  | -5.00 | -5.30 | V                  |
|                                | T – Pkg: $I_O = 5\text{mA to } 500\text{mA}$ , $P \leq 20\text{W}$                    | -4.85   | -5.00 | -5.15 | -4.70  | -5.00 | -5.30 | V                  |
| Quiescent Current              | Over Temperature Range                                                                |         |       | 2.5   |        |       | 2.5   | mA                 |
|                                | $T_J = 25^{\circ}\text{C}$                                                            |         |       | 2.0   |        |       | 2.0   | mA                 |
| Quiescent Current Change       | With Line: $V_{\text{IN}} = -8\text{V to } -25\text{V}$                               |         |       | 1.3   |        |       | 1.3   | mA                 |
|                                | With Load: $I_O = 5\text{mA to } 1.0\text{A}$ (Power Pkgs.)                           |         |       | 0.5   |        |       | 0.5   | mA                 |
|                                | $I_O = 5\text{mA to } 500\text{mA}$ (T)                                               |         |       | 0.5   |        |       | 0.5   | mA                 |
| Dropout Voltage                | $\Delta V_O = 100\text{mV}$ , $T_J = 25^{\circ}\text{C}$                              |         |       |       |        |       |       |                    |
|                                | Power Pkgs: $I_O = 1.0\text{A}$ , T-Pkg: $I_O = 500\text{mA}$                         |         | 1.1   | 2.3   |        | 1.1   | 2.3   | V                  |
| Peak Output Current            | Power Pkgs: $T_J = 25^{\circ}\text{C}$                                                | 1.5     |       | 3.3   | 1.5    |       | 3.3   | A                  |
|                                | T – Pkg: $T_J = 25^{\circ}\text{C}$                                                   | 0.5     |       | 1.4   | 0.5    |       | 1.4   | A                  |
| Short Circuit Current          | Power Pkgs: $V_{\text{IN}} = -35\text{V}$ , $T_J = 25^{\circ}\text{C}$                |         |       | 1.2   |        |       | 1.2   | A                  |
|                                | T – Pkg: $V_{\text{IN}} = -35\text{V}$ , $T_J = 25^{\circ}\text{C}$                   |         |       | 0.6   |        |       | 0.6   | A                  |
| Ripple Rejection               | $\Delta V_{\text{IN}} = 10\text{V}$ , $f = 120\text{Hz}$ , $T_J = 25^{\circ}\text{C}$ | 54      |       |       | 54     |       |       | dB                 |
| Output Noise Voltage (rms)     | $f = 10\text{Hz to } 100\text{kHz}$ (Note 2)                                          |         | 25    | 80    |        | 25    | 80    | $\mu\text{V/V}$    |
| Long Term Stability            | 1000 hours @ $T_J = 125^{\circ}\text{C}$                                              |         | 20    |       |        | 20    |       | mV                 |
| Thermal Shutdown               | $I_O = 5\text{mA}$                                                                    |         | 175   |       |        | 175   |       | $^{\circ}\text{C}$ |

Note 1: All regulation tests are made at constant junction temperature with low duty cycle testing.  
 2: This test is guaranteed but is not tested in production.

**ELECTRICAL CHARACTERISTICS**

Unless otherwise specified, these specifications apply over the operating ambient temperatures for SG7912A / SG7912 with  $-55^{\circ}\text{C} \leq T_A \leq 125^{\circ}\text{C}$ ,  $V_{\text{IN}} = -19\text{V}$ ,  $I_O = 500\text{mA}$  for the K, G, and IG – Power Packages,  $I_O = 100\text{mA}$  for the T and L packages,  $C_{\text{IN}} = 2\mu\text{F}$ , and  $C_{\text{OUT}} = 1\mu\text{F}$ . Low duty cycle pulse testing techniques are used which maintains junction and case temperatures equal to the ambient temperature.

| Parameter                      | Test Conditions                                                                       | SG7912A |       |       | SG7912 |       |       | Units              |
|--------------------------------|---------------------------------------------------------------------------------------|---------|-------|-------|--------|-------|-------|--------------------|
|                                |                                                                                       | Min     | Typ   | Max   | Min    | Typ   | Max   |                    |
| Output Voltage                 | $T_J = 25^{\circ}\text{C}$                                                            | -11.8   | -12.0 | -12.2 | -11.5  | -12.0 | -12.5 | V                  |
| Line Regulation (Note 1)       | $V_{\text{IN}} = -14.5\text{V to } -30\text{V}$ , $T_J = 25^{\circ}\text{C}$          |         | 4     | 60    |        | 10    | 120   | mV                 |
|                                | $V_{\text{IN}} = -16\text{V to } -22\text{V}$ , $T_J = 25^{\circ}\text{C}$            |         | 3     | 30    |        | 3     | 60    | mV                 |
| Load Regulation (Note 1)       | Power Pkgs: $I_O = 5\text{mA to } 1.5\text{A}$ , $T_J = 25^{\circ}\text{C}$           |         | 20    | 90    |        | 12    | 120   | mV                 |
|                                | $I_O = 250\text{mA to } 750\text{mA}$ , $T_J = 25^{\circ}\text{C}$                    |         | 10    | 40    |        | 10    | 60    | mV                 |
|                                | T – Pkg: $I_O = 5\text{mA to } 500\text{mA}$ , $T_J = 25^{\circ}\text{C}$             |         | 10    | 40    |        | 10    | 240   | mV                 |
| Total Output Voltage Tolerance | $V_{\text{IN}} = -14.5\text{V to } -27\text{V}$                                       |         |       |       |        |       |       |                    |
|                                | Power Pkgs: $I_O = 5\text{mA to } 1.0\text{A}$ , $P \leq 20\text{W}$                  | -11.7   | -12.0 | -12.3 | -11.4  | -12.0 | -12.6 | V                  |
|                                | T – Pkg: $I_O = 5\text{mA to } 500\text{mA}$ , $P \leq 2\text{W}$                     | -11.7   | -12.0 | -12.3 | -11.4  | -12.0 | -12.6 | V                  |
| Quiescent Current              | Over Temperature Range                                                                |         |       | 4     |        |       | 4     | mA                 |
|                                | $T_J = 25^{\circ}\text{C}$                                                            |         |       | 3     |        |       | 3     | mA                 |
| Quiescent Current Change       | With Line: $V_{\text{IN}} = -14.5\text{V to } -30\text{V}$                            |         |       | 1.0   |        |       | 1.0   | mA                 |
|                                | With Load: $I_O = 5\text{mA to } 1.0\text{A}$ (Power Pkgs.)                           |         |       | 0.5   |        |       | 0.5   | mA                 |
|                                | $I_O = 5\text{mA to } 500\text{mA}$ (T)                                               |         |       | 0.5   |        |       | 0.5   | mA                 |
| Dropout Voltage                | $\Delta V_O = 100\text{mV}$ , $T_J = 25^{\circ}\text{C}$                              |         |       |       |        |       |       |                    |
|                                | Power Pkgs: $I_O = 1.0\text{A}$ , T – Pkg: $I_O = 500\text{mA}$                       |         | 1.1   | 2.3   |        | 1.1   | 2.3   | V                  |
| Peak Output Current            | Power Pkgs: $T_J = 25^{\circ}\text{C}$                                                | 1.5     |       | 3.3   | 1.5    |       | 3.3   | A                  |
|                                | T – Pkg: $T_J = 25^{\circ}\text{C}$                                                   | 0.5     |       | 1.4   | 0.5    |       | 1.4   | A                  |
| Short Circuit Current          | Power Pkgs: $V_{\text{IN}} = -35\text{V}$ , $T_J = 25^{\circ}\text{C}$                |         |       | 1.2   |        |       | 0.2   | A                  |
|                                | T – Pkg: $V_{\text{IN}} = -35\text{V}$ , $T_J = 25^{\circ}\text{C}$                   |         |       | 0.6   |        |       | 0.6   | A                  |
| Ripple Rejection               | $\Delta V_{\text{IN}} = 10\text{V}$ , $f = 120\text{Hz}$ , $T_J = 25^{\circ}\text{C}$ | 54      |       |       | 54     |       |       | dB                 |
| Output Noise Voltage (rms)     | $f = 10\text{Hz to } 100\text{kHz}$ (note 2)                                          |         | 25    | 80    |        | 25    | 80    | $\mu\text{V/V}$    |
| Long Term Stability            | 1000 hours @ $T_J = 125^{\circ}\text{C}$                                              |         | 60    |       |        | 60    |       | mV                 |
| Thermal Shutdown               | $I_O = 5\text{mA}$                                                                    |         | 175   |       |        | 175   |       | $^{\circ}\text{C}$ |

Note 1: All regulation tests are made at constant junction temperature with low duty cycle testing.  
 2: This test is guaranteed but is not tested in production.

**ELECTRICAL CHARACTERISTICS**






Unless otherwise specified, these specifications apply over the operating ambient temperatures for SG7915A / SG7915 with  $-55^{\circ}\text{C} \leq T_A \leq 125^{\circ}\text{C}$ ,  $V_{\text{IN}} = -23\text{V}$ ,  $I_O = 500\text{mA}$  for the K, G, and IG – Power Packages,  $I_O = 100\text{mA}$  for the T and L packages,  $C_{\text{IN}} = 2\mu\text{F}$ , and  $C_{\text{OUT}} = 1\mu\text{F}$ . Low duty cycle pulse testing techniques are used which maintains junction and case temperatures equal to the ambient temperature.

| Parameter                      | Test Conditions                                                                       | SG7915A |       |       | SG7915 |        |        | Units           |
|--------------------------------|---------------------------------------------------------------------------------------|---------|-------|-------|--------|--------|--------|-----------------|
|                                |                                                                                       | Min     | Typ   | Max   | Min    | Typ    | Max    |                 |
| Output Voltage                 | $T_J = 25^{\circ}\text{C}$                                                            | -14.8   | -15.0 | -15.2 | -14.4  | -15.0  | -15.6  | V               |
| Line Regulation (Note 1)       | $V_{\text{IN}} = -17.5\text{V to } -30\text{V}$ , $T_J = 25^{\circ}\text{C}$          |         | 5     | 75    |        | 11     | 150    | mV              |
|                                | $V_{\text{IN}} = -20\text{V to } -25\text{V}$ , $T_J = 25^{\circ}\text{C}$            |         | 3     | 40    |        | 3      | 75     | mV              |
| Load Regulation (Note 1)       | Power Pkgs: $I_O = 5\text{mA to } 1.5\text{A}$ , $T_J = 25^{\circ}\text{C}$           |         | 30    | 100   |        | 12     | 150    | mV              |
|                                | $I_O = 250\text{mA to } 750\text{mA}$ , $T_J = 25^{\circ}\text{C}$                    |         | 4     | 50    |        | 4      | 75     | mV              |
|                                | T – Pkg: $I_O = 5\text{mA to } 500\text{mA}$ , $T_J = 25^{\circ}\text{C}$             |         | 10    | 50    |        | 10     | 240    |                 |
| Total Output Voltage Tolerance | $V_{\text{IN}} = -18.5\text{V to } -30\text{V}$                                       |         |       |       |        |        |        |                 |
|                                | Power Pkgs: $I_O = 5\text{mA to } 1.0\text{A}$ , $P \leq 20\text{W}$                  | -14.6   | -15.0 | -15.4 | -14.25 | -15.00 | -15.75 | V               |
|                                | T – Pkg: $I_O = 5\text{mA to } 500\text{mA}$ , $P \leq 2\text{W}$                     | -14.6   | -15.0 | -15.4 | -14.25 | -15.00 | -15.75 | V               |
| Quiescent Current              | Over Temperature Range                                                                |         |       | 4     |        |        | 4      | mA              |
|                                | $T_J = 25^{\circ}\text{C}$                                                            |         |       | 3     |        |        | 3      | mA              |
| Quiescent Current Change       | With Line: $V_{\text{IN}} = -18.5\text{V to } -30\text{V}$                            |         |       | 1.0   |        |        | 1.0    | mA              |
|                                | With Load: $I_O = 5\text{mA to } 1.0\text{A}$ (Power Pkgs)                            |         |       | 0.5   |        |        | 0.5    | mA              |
|                                | $I_O = 5\text{mA to } 500\text{mA}$ (T)                                               |         |       | 0.5   |        |        | 0.5    | mA              |
| Dropout Voltage                | $\Delta V_O = 100\text{mV}$ , $T_J = 25^{\circ}\text{C}$                              |         |       |       |        |        |        |                 |
|                                | Power Pkgs: $I_O = 1.0\text{A}$ , T – Pkg: $I_O = 500\text{mA}$                       |         | 1.1   | 2.3   |        | 1.1    | 2.3    | V               |
| Peak Output Current            | Power Pkgs: $T_J = 25^{\circ}\text{C}$                                                | 1.5     |       | 3.3   | 1.5    |        | 3.3    | A               |
|                                | T – Pkg: $T_J = 25^{\circ}\text{C}$                                                   | 0.5     |       | 1.4   | 0.5    |        | 1.4    | A               |
| Short Circuit Current          | Power Pkgs: $V_{\text{IN}} = -35\text{V}$ , $T_J = 25^{\circ}\text{C}$                |         |       | 1.2   |        |        | 1.2    | A               |
|                                | T – Pkg: $V_{\text{IN}} = -35\text{V}$ , $T_J = 25^{\circ}\text{C}$                   |         |       | 0.6   |        |        | 0.6    | A               |
| Ripple Rejection               | $\Delta V_{\text{IN}} = 10\text{V}$ , $f = 120\text{Hz}$ , $T_J = 25^{\circ}\text{C}$ | 54      |       |       | 54     |        |        | dB              |
| Output Noise Voltage (rms)     | $f = 10\text{Hz to } 100\text{kHz}$ (note 2)                                          |         | 25    | 80    |        | 25     | 80     | $\mu\text{V/V}$ |
| Long Term Stability            | 1000 hours @ $T_J = 125^{\circ}\text{C}$                                              |         | 60    |       |        | 60     |        | mV              |
| Thermal Shutdown               | $I_O = 5\text{mA}$                                                                    |         | 175   |       |        | 175    |        |                 |

Note 1: All regulation tests are made at constant junction temperature with low duty cycle testing.  
 2: This test is guaranteed but is not tested in production.

**NOTES**

**CONNECTION DIAGRAMS & ORDERING INFORMATION (SEE NOTES BELOW)**

| Package                                                         | Part No.       | Ambient Temperature Range | Connection Diagram                                                                    |
|-----------------------------------------------------------------|----------------|---------------------------|---------------------------------------------------------------------------------------|
| 3-Terminal TO-3 Metal Can<br>K – Package                        | SG79xxAK/883B  | -55°C to 125°C            |    |
|                                                                 | SG7905AK/DESC  | -55°C to 125°C            |                                                                                       |
|                                                                 | SG7912AK/DESC  | -55°C to 125°C            |                                                                                       |
|                                                                 | SG7915AK/DESC  | -55°C to 125°C            |                                                                                       |
|                                                                 | SG79xxAK       | -55°C to 125°C            |                                                                                       |
|                                                                 | SG79xxK/883B   | -55°C to 125°C            |                                                                                       |
|                                                                 | JAN7905K       | -55°C to 125°C            |                                                                                       |
|                                                                 | JAN7912K       | -55°C to 125°C            |                                                                                       |
|                                                                 | JAN7915K       | -55°C to 125°C            |                                                                                       |
| 3-Pin TO-39 Metal Can<br>T – Package                            | SG79xxAT/883B  | -55°C to 125°C            |    |
|                                                                 | SG7905AT/DESC  | -55°C to 125°C            |                                                                                       |
|                                                                 | SG7912AT/DESC  | -55°C to 125°C            |                                                                                       |
|                                                                 | SG7915AT/DESC  | -55°C to 125°C            |                                                                                       |
|                                                                 | SG79xxAT       | -55°C to 125°C            |                                                                                       |
|                                                                 | SG79xxT/883B   | -55°C to 125°C            |                                                                                       |
|                                                                 | JAN7905T       | -55°C to 125°C            |                                                                                       |
|                                                                 | JAN7912T       | -55°C to 125°C            |                                                                                       |
|                                                                 | JAN7915T       | -55°C to 125°C            |                                                                                       |
| 3-Pin Hermetic TO-257<br>IG – Package (Isolated)                | SG79xxAIG/883B | -55°C to 125°C            |   |
|                                                                 | SG7905AIG/DESC | -55°C to 125°C            |                                                                                       |
|                                                                 | SG7912AIG/DESC | -55°C to 125°C            |                                                                                       |
|                                                                 | SG7915AIG/DESC | -55°C to 125°C            |                                                                                       |
|                                                                 | SG79xxAIG      | -55°C to 125°C            |                                                                                       |
|                                                                 | SG79xxIG/883B  | -55°C to 125°C            |                                                                                       |
| 20-Pin Ceramic Leadless Chip Carrier<br>L – Package             | SG79xxL/883B   | -55°C to 125°C            |  |
|                                                                 | SG79xxL        | -55°C to 125°C            |                                                                                       |
|                                                                 | SG7905AL/DESC  | -55°C to 125°C            |                                                                                       |
|                                                                 | SG7912AL/DESC  | -55°C to 125°C            |                                                                                       |
|                                                                 | SG7912AL/DESC  | -55°C to 125°C            |                                                                                       |
| 3-Pin Hermetic TO-257<br>G – Package (Case is V <sub>IN</sub> ) | SG79xxAG/883B  | -55°C to 125°C            |  |
|                                                                 | SG7905AG/DESC  | -55°C to 125°C            |                                                                                       |
|                                                                 | SG7912AG/DESC  | -55°C to 125°C            |                                                                                       |
|                                                                 | SG7915AG/DESC  | -55°C to 125°C            |                                                                                       |
|                                                                 | SG79xxAG       | -55°C to 125°C            |                                                                                       |
|                                                                 | SG79xxG/883B   | -55°C to 125°C            |                                                                                       |
|                                                                 | SG79xxG        | -55°C to 125°C            |                                                                                       |

- Note
- 1: Contact factory for JAN and DESC product availability.
  - 2: All parts are viewed from the top.
  - 3: "xx" to be replaced by output voltage of specific fixed regulator.
  - 4: Some products will be available in hermetic flat pack (F). Consult factory for price and availability.
  - 5: Both inputs and outputs must be externally connected together at the device terminals.
  - 6: For normal operation, the V<sub>O</sub> SENSE pin must be externally connected to the load.

PRODUCTION DATA – Information contained in this document is proprietary to Microsemi and is current as of publication date. This document may not be modified in any way without the express written consent of Microsemi. Product processing does not necessarily include testing of all parameters. Microsemi reserves the right to change the configuration and performance of the product and to discontinue product at any time.