

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, —, *

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC

	DIST
--	------

REVISIONS

G

02

	F
--	---

LTR

DESCRIPTION

DATE _____

	DWN
--	-----

	APVD
--	------


A2

REVISÉD PER ECO-13-014538

14SEP2013

KH

DR



- 1 STAMP "AMP 16-14*" LOCATED APPROX AS SHOWN,
TERMINAL IS A 16 IR AND ACCEPTS 16AWG, WIRE ONLY

2 MATERIAL: TERMINAL –
COPPER PER ASTM B-152, ANNEALED.
SLEEVE – NYLON, COLOR BLUE

3 FINISH: TERMINAL –
0.00254 [.000100] MIN TIN PLATE PER ASTM B-545

4 WIRE INSULATION DIA 2-3.3 [.078-.130]

5 TONGUE MATERIAL THK: 0.79 ± 0.05 [.031 $\pm$.002]


6 DIMENSION APPLIES FROM EDGE OF WIRE BARREL
TO CENTER OF STUD HOLE.

7 MAX RECOMMENDED OPERATING TEMP 105°C [221°F]

8 VOLTAGE RATING IS 300 V MAX

9 1.65-2.62mm² [3,260-5,180] CMA, STRANDED

1000	LOOSE PIECE	134122-1
QTY	PACKAGING TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH	19OCT07	 TE Connectivity					
		CHK T MICHIELUTTI	19OCT07						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T MICHIELUTTI	19OCT07	NAME				
		0 PLC ± -	PRODUCT SPEC		TERMINAL, RING TONGUE, I.R., PIDG, WIRE SIZE 14 AWG —				
		1 PLC ± -	—						
		2 PLC ± -	APPLICATION SPEC						
		3 PLC ± 0.20 [.008]	—		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO
		4 PLC ± -			A3	00779	C-134122		—
		ANGLES ± -	WEIGHT —						
MATERIAL		FINISH			SCALE 4:1 SHEET 1 OF 1 REV A2				
CUSTOMER DRAWING									