

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202320023

Status:

Active

Overview:

Brad M23 Signal and Power Connectors

Description:


Brad M23 Signal Connector, Female Insert, Solder Contacts, 12 Poles

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                      |
|-------------------------------|--------------------------------------|
| General                       |                                      |
| Product Family                | Field Attachable / Accessories       |
| Series                        | 120232                               |
| Application                   | Signal                               |
| Comments                      | Insert with Solder Contacts          |
| IP Rating                     | IP67                                 |
| Material - Contact            | N/A                                  |
| Overview                      | Brad M23 Signal and Power Connectors |
| Product Name                  | Brad M23                             |
| Type                          | Field Attachable Connector           |
| UPC                           | 883906205300                         |
| Physical                      |                                      |
| Cable Diameter                | N/A                                  |
| Coupling Type                 | N/A                                  |
| Diagnostics / LEDs            | No                                   |
| Diagnostics Port              | No                                   |
| Gender                        | Female                               |
| Keyway                        | None                                 |
| Material - Connector Body     | Nylon                                |
| Material - Coupling Nut       | N/A                                  |
| Material - Plating Mating     | n/a                                  |
| Net Weight                    | 8.560/g                              |
| Orientation                   | Straight                             |
| Poles                         | 12                                   |
| Temperature Range - Operating | -40°C to +125°C                      |
| Wire Size AWG                 | N/A                                  |
| Electrical                    |                                      |
| Current - Maximum per Contact | N/A                                  |
| Voltage - Maximum             | N/A                                  |
| Material Info                 |                                      |
| Engineering Number            | KISC0-55                             |
| Reference - Drawing Numbers   |                                      |
| Sales Drawing                 | SD-120232-023                        |



Series image - Reference only

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Reviewed                                                  |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Reviewed                                                  |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

120232 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION