

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PREEPORT, ILLINOIS

FED. MFR. CODE 91929

SWITCH — BASIC

CATALOG LISTING

ISE2-3

(M) ISE2-3
REPLACES ISSUE 4

ISE2-3
PAGE 1 OF 1

M

DRAWING
NUMBER

ISSUE
889

RELEASE NO.

CHECK

REVISIONS

A	CO16449	R G C	1 MARCH 82
B	CO-34213	J A L	24 SEPT 74
C	51463-D	WJM	16 JUL 82
D	CO57041A	CJH	21 MAR 85
E	CO94274	DLM	MAR 99

CHECK

EMERGE

DAW


CHECK

62

FORMTEK

FO-50378

FORMTEK



NOTE -

- ▲ MOUNTING HOLES WILL ACCEPT $.087$ MAX DIA PINS OR SCREWS ON $.375 \pm .002$ CENTERS
- ▲ ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- ▲ WEIGHT OF SWITCH ONLY IS $.26$ OZ MAX
WEIGHT OF SWITCH WITH WIRE LEADS IS 1.00 OZ MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE	5-17 OZ
RELEASE FORCE	4 OZ MIN
RELEASE TRAVEL	.004 MIN
DIFFERENTIAL TRAVEL	.004 MAX
OVERTRAVEL	.003 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT	
S P N C	
250 VAC	5 AMP
30 VOLTS DC RATING	
INDUCTIVE	SEA LEVEL — 3 AMP
	50,000 FT — 2.5 AMP
RESISTIVE	SEA LEVEL — 5 AMP
	50,000 FT — 5 AMP
MAXIMUM INRUSH	24 AMP

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm$

WEIGHT

▲