


DESCRIPTION: ABOVE AND BELOW P.C.B., DECK IS AS VIEWED BY USER.

| PRODUCT NO.<br>72305-XXX | STAND-OFF<br>HEIGHT<br>DIM L | (A)<br>HEADER ASSY<br>71249-XXXX | (B)<br>MECHANISM ASSY<br>72304/92791-XXX | (C)<br>MATING<br>RECEPTACLE                                                                        | MOUNTING STYLE TO<br>PCB                                                            |
|--------------------------|------------------------------|----------------------------------|------------------------------------------|----------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 000                      | 0.0                          | 0000                             | 72304-000                                | 100 POSITION<br>(2x50) 0.8mm<br>RECEPTACLE<br><br>PART NO.<br>73277-101000<br><br>ORDER SEPARATELY |  |
| 020                      | 2.2                          | 0022                             | 72304-022                                |                                                                                                    |  |
| 040                      | 4.3                          | 0043                             | 72304-043                                |                                                                                                    |  |
| 050                      | 5.0                          | 0050                             | 72304-050                                |                                                                                                    |  |
| 005                      | 0.0                          | 0500                             | 72304-000                                |                                                                                                    |                                                                                     |
| 025                      | 0.0                          | 0522                             | 72304-000                                |                                                                                                    |                                                                                     |
| 045                      | 0.0                          | 0543                             | 72304-000                                |                                                                                                    |                                                                                     |
| 055                      | 0.0                          | 0550                             | 72304-000                                |                                                                                                    |                                                                                     |
|                          |                              |                                  |                                          |                                                                                                    |                                                                                     |
| 520                      | 2.2                          | 5022                             | 92791-022S                               |                                                                                                    |                                                                                     |
| 540                      | 4.3                          | 5043                             | 92791-043S                               |                                                                                                    |                                                                                     |
| 550                      | 5.0                          | 5050                             | △ 92791-052                              |                                                                                                    |                                                                                     |
|                          |                              |                                  |                                          |                                                                                                    |                                                                                     |
| 525                      | 0.0                          | 5522                             | 92791-001S                               |                                                                                                    |                                                                                     |
| 545                      | 0.0                          | 5543                             | 92791-001S                               |                                                                                                    |                                                                                     |
| 555                      | 0.0                          | 5550                             | 92791-001S                               |                                                                                                    |                                                                                     |

NOTE:

- SEE 72306 FOR DOUBLE DECK ASSEMBLY



ORDERING INFORMATION

ORDER:

- EJECT HEADER ASSY (72305-XXX)
- MATING RECEPTACLE (73277-101000)

|                |              |     |    |          |   |                                       |           |                                                                                       |   |                       |       |
|----------------|--------------|-----|----|----------|---|---------------------------------------|-----------|---------------------------------------------------------------------------------------|---|-----------------------|-------|
| mat'l. code    |              |     |    | surface  |   | tolerance                             |           | projection                                                                            |   | product family        |       |
|                |              |     |    | ISO 1302 |   | ISO 406 ISO 1181                      |           |  |   | CARDBUS               |       |
| ltr            | ecn          | no  | dr | date     |   | tolerances unless otherwise specified |           |                                                                                       |   |                       |       |
| E              | V02257       | TFG |    | 11/3/00  |   | angles                                |           | linear                                                                                |   | title                 |       |
| F              | N05-0074     | WB  |    | 03/14/05 |   | ±2°                                   |           |                                                                                       |   | CARDBUS SINGLE DECK   |       |
| G              | N06-0012     | MZ  |    | 01/16'06 |   |                                       |           |                                                                                       |   | ASS'Y SMT TYPE 123    |       |
| H              | N06-0129     | M.Z |    | 05/11'06 |   | dr                                    | Mike Zhou | 05/10/06                                                                              |   | dwg no                |       |
| J              | N07-0109     | DT  |    | 5/7/07   |   | engr                                  | Mike Zhou | 05/10/06                                                                              |   | sheet 1 of 11 size    |       |
| K              | N08-0028     | MZ  |    | 2/25'08  |   | chr                                   | Mike Zhou | 05/10/06                                                                              |   | 72305 A4              |       |
| L              | BLX-N-011409 | ZK  |    | 04/07/12 |   | appa                                  | Qin David | 05/10/06                                                                              |   | type CUSTOMER Drawing |       |
| sheet revision |              |     |    | L        | L | L                                     | L         | L                                                                                     | L | L                     | L     |
| index sheet    |              |     |    | 1        | 2 | 3                                     | 4         | 5                                                                                     | 6 | 7                     | 8     |
|                |              |     |    |          |   |                                       |           |                                                                                       |   | 9                     | 10 11 |

DESCRIPTION: ABOVE AND BELOW P.C.B., DECK IS AS VIEWED BY USER.

| PRODUCT NO.<br>72305-XXX | STAND-OFF<br>HEIGHT<br>DIM L | Ⓐ<br>HEADER ASSY<br>71249-XXXX | Ⓑ<br>MECHANISM ASSY<br>72304/92791-XXX | Ⓒ<br>MATING<br>RECEPTACLE                                                                    | MOUNTING STYLE TO<br>PCB                                                            |
|--------------------------|------------------------------|--------------------------------|----------------------------------------|----------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| 000LF                    | 0.0                          | 0000LF                         | 72304-000                              | 100 POSITION<br>(2x50) 0.8mm<br>RECEPTACLE<br>PART NO.<br>73277-101402LF<br>ORDER SEPARATELY |  |
| 020LF                    | 2.2                          | 0022LF                         | 72304-022                              |                                                                                              |  |
| 040LF                    | 4.3                          | 0043LF                         | 72304-043                              |                                                                                              |  |
| 050LF                    | 5.0                          | 0050LF                         | 72304-050                              |                                                                                              |  |
| 005LF                    | 0.0                          | 0500LF                         | 72304-000                              |                                                                                              |                                                                                     |
| 025LF                    | 0.0                          | 0522LF                         | 72304-000                              |                                                                                              |                                                                                     |
| 045LF                    | 0.0                          | 0543LF                         | 72304-000                              |                                                                                              |                                                                                     |
| 055LF                    | 0.0                          | 0550LF                         | 72304-000                              |                                                                                              |                                                                                     |
|                          |                              |                                |                                        |                                                                                              |                                                                                     |
| 520LF                    | 2.2                          | 5022LF                         | 92791-022S                             |                                                                                              |                                                                                     |
| 540LF                    | 4.3                          | 5043LF                         | 92791-043S                             |                                                                                              |                                                                                     |
| 550LF                    | 5.0                          | 5050LF                         | ⚠ 92791-052                            |                                                                                              |                                                                                     |
|                          |                              |                                |                                        |                                                                                              |                                                                                     |
| 525LF                    | 0.0                          | 5522LF                         | 92791-001S                             |                                                                                              |                                                                                     |
| 545LF                    | 0.0                          | 5543LF                         | 92791-001S                             |                                                                                              |                                                                                     |
| 555LF                    | 0.0                          | 5550LF                         | 92791-001S                             |                                                                                              |                                                                                     |

## NOTE:

- SEE 72306 FOR DOUBLE DECK ASSEMBLY
- IF LEAD FREE P/N.THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- IF LEAD FREE P/N.THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008
- LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION



## ORDERING INFORMATION

## ORDER:


- EJECT HEADER ASSY (72305-XXXLF)
- MATING RECEPTACLE (73277-101000LF)

|                    |  |                                       |  |           |  |            |  |                                            |  |
|--------------------|--|---------------------------------------|--|-----------|--|------------|--|--------------------------------------------|--|
| mat'l. code        |  | surface                               |  | tolerance |  | projection |  | product family                             |  |
| ISO 1302           |  | ISO 406                               |  | ISO 1181  |  | 100        |  | CARDBUS                                    |  |
| ltr ecn no dr date |  | tolerances unless otherwise specified |  | linear    |  | MM         |  | title                                      |  |
| L                  |  | angles                                |  | linear    |  | scale 4    |  | CARD BUS SINGLE DECK<br>ASS'Y SMT TYPE 123 |  |
|                    |  | ±2°                                   |  |           |  |            |  | dwg no                                     |  |
|                    |  | dr                                    |  | Mike Zhou |  | 05/10/06   |  | sheet 2 of 11                              |  |
|                    |  | engr                                  |  | Mike Zhou |  | 05/10/06   |  | size                                       |  |
|                    |  | chr                                   |  | Mike Zhou |  | 05/10/06   |  | A 4                                        |  |
|                    |  | appd                                  |  | Qin David |  | 05/10/06   |  | type CUSTOMER Drawing                      |  |
| sheet index        |  | revision sheet                        |  |           |  |            |  |                                            |  |

|                |
|----------------|
| PRODUCT NUMBER |
| 72305-***      |
| 72305-***LF    |



MATING RECEPTACLE SHOWN FOR APPLICATION CLARITY ONLY. MUST BE ORDERED SEPARATELY




|                    |                |                                       |           |            |                                        |
|--------------------|----------------|---------------------------------------|-----------|------------|----------------------------------------|
| mat'l. code        |                | surface                               | tolerance | projection | product family                         |
| ISO 1302           |                | ISO 406                               | ISO 101   |            | CARDBUS                                |
| ltr ecn naddr date |                | tolerances unless otherwise specified |           |            | title                                  |
| L                  |                | angles                                | linear    | MM         | CARDBUS SINGLE DECK ASS'Y SMT TYPE 123 |
|                    |                | ±2°                                   |           | scale      | dwg no                                 |
|                    |                | dr                                    | Mike Zhou | 05/10/06   | sheet 3 of 11                          |
|                    |                | enr                                   | Mike Zhou | 05/10/06   | size                                   |
|                    |                | chr                                   | Mike Zhou | 05/10/06   | A 4                                    |
|                    |                | app                                   | Qin David | 05/10/06   | type CUSTOMER Drawing                  |
| sheet index        | revision sheet |                                       |           |            |                                        |


PRODUCT NUMBER

72305-\*\*\*




72305-\*\*\*LF



MATING RECEPTACLE SHOWN  
FOR APPLICATION CLARITY ONLY.  
MUST BE ORDERED SEPARATELY



VIEW A-A




|             |  |          |  |          |  |                  |  |                                       |  |                     |  |               |  |          |  |
|-------------|--|----------|--|----------|--|------------------|--|---------------------------------------|--|---------------------|--|---------------|--|----------|--|
| mat'l. code |  |          |  | surface  |  | tolerance        |  | projection                            |  | product family      |  |               |  |          |  |
|             |  |          |  | ISO 1302 |  | ISO 406 ISO 1:01 |  |                                       |  | CARDBUS             |  |               |  |          |  |
| ltn         |  | ecn no   |  | dr       |  | date             |  | tolerances unless otherwise specified |  | title               |  |               |  |          |  |
| L           |  |          |  |          |  |                  |  |                                       |  | CARDBUS SINGLE DECK |  |               |  |          |  |
|             |  |          |  |          |  |                  |  | linear                                |  | ASS'Y SMT TYPE 123  |  |               |  |          |  |
|             |  |          |  |          |  |                  |  |                                       |  |                     |  |               |  |          |  |
|             |  |          |  |          |  |                  |  | ±2'                                   |  | scale               |  |               |  |          |  |
|             |  |          |  | dr       |  | Mike Zhou        |  | 05/10/06                              |  | dwg no              |  | sheet 4 of 11 |  | size     |  |
|             |  |          |  | enr      |  | Mike Zhou        |  | 05/10/06                              |  |                     |  | 72305         |  | A 4      |  |
|             |  |          |  | chr      |  | Mike Zhou        |  | 05/10/06                              |  |                     |  |               |  |          |  |
|             |  |          |  | app      |  | Qin David        |  | 05/10/06                              |  |                     |  |               |  |          |  |
|             |  |          |  |          |  |                  |  |                                       |  |                     |  | type          |  | CUSTOMER |  |
|             |  |          |  |          |  |                  |  |                                       |  |                     |  |               |  | Drawing  |  |
| sheet       |  | revision |  |          |  |                  |  |                                       |  |                     |  |               |  |          |  |
| index       |  | sheet    |  |          |  |                  |  |                                       |  |                     |  |               |  |          |  |

FCI CONFIDENTIAL





FCI  
FCIconnect.com

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of this information shown on this document may be used in any way or disclosed to others without the written consent of FCI.  
Copyright FCI.

|                |
|----------------|
| PRODUCT NUMBER |
| 72305-***      |
| 72305-***LF    |



MATING RECEPTACLE SHOWN  
FOR APPLICATION CLARITY ONLY.  
MUST BE ORDERED SEPARATELY




|                   |                                       |                    |            |                                        |
|-------------------|---------------------------------------|--------------------|------------|----------------------------------------|
| mat'l. code       | surface                               | tolerance          | projection | product family                         |
|                   | ISO 1302                              | ISO 406 ISO 101    |            | CARDBUS                                |
| ltr ecn nldr date | tolerances unless otherwise specified |                    |            |                                        |
| L                 | angles                                | linear             | MM         | CARDBUS SINGLE DECK ASS'Y SMT TYPE 123 |
|                   | ±2°                                   |                    | scale      |                                        |
|                   | dr                                    | Mike Zhou 05/10/06 |            | dwg no                                 |
|                   | enr                                   | Mike Zhou 05/10/06 |            | 72305                                  |
|                   | chr                                   | Mike Zhou 05/10/06 |            | type CUSTOMER                          |
|                   | appd                                  | Qin David 05/10/06 |            | Drawing                                |
| sheet index       | revision sheet                        |                    |            |                                        |

FCI CONFIDENTIAL



FCI  
FCIconnect.com

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of this information shown on this document may be used in any way or disclosed to others without the written consent of FCI.  
Copyright FCI.

|                |
|----------------|
| PRODUCT NUMBER |
| 72305-***      |
| 72305-***LF    |



MATING RECEPTACLE SHOWN  
FOR APPLICATION CLARITY ONLY.  
MUST BE ORDERED SEPARATELY




|                   |                                       |                  |            |                                        |
|-------------------|---------------------------------------|------------------|------------|----------------------------------------|
| mat'l. code       | surface                               | tolerance        | projection | product family                         |
|                   | ISO 1302                              | ISO 406 ISO 1101 |            | CARDBUS                                |
| ltr ecn nldr date | tolerances unless otherwise specified |                  |            |                                        |
| L                 | angles                                | linear           | MM         | CARDBUS SINGLE DECK ASS'Y SMT TYPE 123 |
|                   | ±2°                                   |                  | scale 4    |                                        |
|                   | dr                                    | Mike Zhou        | 05/10/06   | dwg no                                 |
|                   | enr                                   | Mike Zhou        | 05/10/06   | sheet 6 of 11                          |
|                   | chr                                   | Mike Zhou        | 05/10/06   | size                                   |
|                   | app                                   | Qin David        | 05/10/06   | A 4                                    |
| sheet index       | revision sheet                        |                  |            | type CUSTOMER Drawing                  |

FCI CONFIDENTIAL



FCI  
FCIconnect.com

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of this information shown on this document may be used in any way or disclosed to others without the written consent of FCI.  
Copyright FCI.

|                |
|----------------|
| PRODUCT NUMBER |
| 72305-***      |
| 72305-***LF    |




MATING RECEPTACLE SHOWN FOR APPLICATION CLARITY ONLY. MUST BE ORDERED SEPARATELY



|                   |                                       |                  |            |                                        |
|-------------------|---------------------------------------|------------------|------------|----------------------------------------|
| mat'l. code       | surface                               | tolerance        | projection | product family                         |
|                   | ISO 1302                              | ISO 406 ISO 1101 |            | CARDBUS                                |
| ltr ecn nodr date | tolerances unless otherwise specified |                  |            | title                                  |
| L                 | angles                                | linear           | MM         | CARDBUS SINGLE DECK ASS'Y SMT TYPE 123 |
|                   | ±2°                                   |                  | scale 4    |                                        |
|                   | dr                                    | Mike Zhou        | 05/10/06   | dwg no                                 |
|                   | engr                                  | Mike Zhou        | 05/10/06   | sheet 7 of 11                          |
|                   | chr                                   | Mike Zhou        | 05/10/06   | size                                   |
|                   | appd                                  | Qin David        | 05/10/06   | A 4                                    |
| sheet             | revision                              |                  |            | type                                   |
| index             | sheet                                 |                  |            | CUSTOMER Drawing                       |

# P.C.B. LAYOUT FOR 0mm STANDOFF



|             |          |          |                  |            |                                        |
|-------------|----------|----------|------------------|------------|----------------------------------------|
| mat'l. code |          | surface  | tolerance        | projection | product family                         |
|             |          | ISO 1302 | ISO 406 ISO 1101 |            | CARDBUS                                |
| ltr         | ecn      | no       | dr               | date       | title                                  |
| L           |          |          |                  |            | CARDBUS SINGLE DECK ASS'Y SMT TYPE 123 |
|             |          |          | angles           | linear     | MM                                     |
|             |          |          | ±2°              | scale 4    |                                        |
|             |          | dr       | Mike Zhou        | 05/10/06   | dwg no                                 |
|             |          | engr     | Mike Zhou        | 05/10/06   | sheet 8 of 11                          |
|             |          | chr      | Mike Zhou        | 05/10/06   | size                                   |
|             |          | appd     | Qin David        | 05/10/06   | A 4                                    |
| sheet       | revision |          |                  |            | type                                   |
| index       | sheet    |          |                  |            | CUSTOMER Drawing                       |





Information shown  
is shared to others

**FCI**

FCIconnect.com

D

## A



C

| HEADER PINOUT | TYPE | BTB 100 POS RECEPTACLE | HEADER PINOUT | TYPE | BTB 100 POS RECEPTACLE | SHIELD PINOUT | TYPE | BTB 100 POS RECEPTACLE |
|---------------|------|------------------------|---------------|------|------------------------|---------------|------|------------------------|
| 1             | GND  | 1                      | 35            | GND  | 51                     | 1             | GND  | 4 & 54                 |
| 2             | SIG  | 2                      | 36            | DET  | 52                     | 2             | GND  | 7 & 57                 |
| 3             | SIG  | 3                      | 37            | SIG  | 53                     | 3             | GND  | 10 & 60                |
| 4             | SIG  | 5                      | 38            | SIG  | 55                     | 4             | GND  | 13 & 63                |
| 5             | SIG  | 6                      | 39            | SIG  | 56                     | 5             | GND  | 16 & 66                |
| 6             | SIG  | 8                      | 40            | SIG  | 58                     | 6             | GND  | 19 & 69                |
| 7             | SIG  | 9                      | 41            | SIG  | 59                     | 7             | GND  | 22 & 72                |
| 8             | SIG  | 11                     | 42            | SIG  | 61                     | 8             | GND  | 25 & 75                |
| 9             | SIG  | 12                     | 43            | SIG  | 62                     | 9             | GND  | 26 & 76                |
| 10            | SIG  | 14                     | 44            | SIG  | 64                     | 10            | GND  | 29 & 79                |
| 11            | SIG  | 15                     | 45            | SIG  | 65                     | 11            | GND  | 32 & 82                |
| 12            | SIG  | 17                     | 46            | SIG  | 67                     | 12            | GND  | 35 & 85                |
| 13            | SIG  | 18                     | 47            | SIG  | 68                     | 13            | GND  | 38 & 88                |
| 14            | SIG  | 20                     | 48            | SIG  | 70                     | 14            | GND  | 41 & 91                |
| 15            | SIG  | 21                     | 49            | SIG  | 71                     | 15            | GND  | 44 & 94                |
| 16            | SIG  | 23                     | 50            | SIG  | 73                     | 16            | GND  | 47 & 97                |
| 17            | PWR  | 24                     | 51            | PWR  | 74                     |               |      |                        |
| 18            | SIG  | 27                     | 52            | SIG  | 77                     |               |      |                        |
| 19            | SIG  | 28                     | 53            | SIG  | 78                     |               |      |                        |
| 20            | SIG  | 30                     | 54            | SIG  | 80                     |               |      |                        |
| 21            | SIG  | 31                     | 55            | SIG  | 81                     |               |      |                        |
| 22            | SIG  | 33                     | 56            | SIG  | 83                     |               |      |                        |
| 23            | SIG  | 34                     | 57            | SIG  | 84                     |               |      |                        |
| 24            | SIG  | 36                     | 58            | SIG  | 86                     |               |      |                        |
| 25            | SIG  | 37                     | 59            | SIG  | 87                     |               |      |                        |
| 26            | SIG  | 39                     | 60            | SIG  | 89                     |               |      |                        |
| 27            | SIG  | 40                     | 61            | SIG  | 90                     |               |      |                        |
| 28            | SIG  | 42                     | 62            | SIG  | 92                     |               |      |                        |
| 29            | SIG  | 43                     | 63            | SIG  | 93                     |               |      |                        |
| 30            | SIG  | 45                     | 64            | SIG  | 95                     |               |      |                        |
| 31            | SIG  | 46                     | 65            | SIG  | 96                     |               |      |                        |
| 32            | SIG  | 48                     | 66            | SIG  | 98                     |               |      |                        |
| 33            | SIG  | 49                     | 67            | DET  | 99                     |               |      |                        |
| 34            | GND  | 50                     | 68            | GND  | 100                    |               |      |                        |

NOTES:

- 1 ORDER MATING RECEPTACLE SEPARATELY.
- 2 RECOMMENDED SCREW TORQUE: 1.0 TO 1.5 MAX in-lbs. (1.2-1.7 cm-kgs).  
RECOMMENDED HOLD-DOWN - 2mm SCREWS (95121) AND HEX NUTS (92869).
- 3 MATERIAL:
- 3.1 HEADER ASSY:  
PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK - ABOVE PCB  
HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK - BELOW PCB  
PIN: PHOSPHOR BRONZE  
PCB: FR4
- 3.2 MECHANISM ASSY:  
PLASTIC GUIDE: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK  
COVER PLATE: STAINLESS STEEL  
EMI CONTACT: PHOSPHOR BRONZE
- 3.3 .8 BTB RECEPTACLE (73277-101000):  
PLASTIC: HIGH TEMPERATURE THERMOPLASTIC UL94V-0 BLACK  
CONTACT: BeCu
- 4 FINISH (PIN)  
UNDER PLATING: 0.5um Ni  
CONTACT AREA: 0.076 μm MIN. GOLD
- SOLDER TAIL: 2.5um Sn-Pb FOR TIN LEAD OPTION  
2.5um PURE TIN FOR LEAD FREE OPTION
- ⑤ DIM "X"
- |          |         |                  |
|----------|---------|------------------|
| 4.25±0.1 | 3.5±0.1 | 5.0±0.1          |
| OTHERS   | 36,67   | 1,17,34,35,51,68 |
- 6 IF LEAD FREE P/N.THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
- 7 IF LEAD FREE P/N.THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008
- 8 LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION
- 9 PRODUCT SPEC:110-263

|                   |  |                                      |  |                 |  |            |  |                     |  |
|-------------------|--|--------------------------------------|--|-----------------|--|------------|--|---------------------|--|
| mat'l. code       |  | surface                              |  | tolerance       |  | projection |  | product family      |  |
|                   |  | ISO 1302                             |  | ISO 406 ISO 101 |  |            |  | CARDBUS             |  |
| ltr ecn nodr date |  | tolerances unless otherwisespecified |  | title           |  |            |  |                     |  |
| L                 |  | angles                               |  | linear          |  | MM         |  | CARDBUS SINGLE DECK |  |
|                   |  | ±2°                                  |  |                 |  | scale 4    |  | ASS'Y SMT TYPE 123  |  |
|                   |  | dr                                   |  | Mike Zhou       |  | 05/10/06   |  | dwg no              |  |
|                   |  | engr                                 |  | Mike Zhou       |  | 05/10/06   |  | sheet11of11size     |  |
|                   |  | chr                                  |  | Mike Zhou       |  | 05/10/06   |  | 72305               |  |
|                   |  | appa                                 |  | Qin David       |  | 05/10/06   |  | A 4                 |  |
|                   |  |                                      |  |                 |  |            |  | type CUSTOMER       |  |
|                   |  |                                      |  |                 |  |            |  | Drawing             |  |
| sheet             |  | revision                             |  |                 |  |            |  |                     |  |
| index             |  | sheet                                |  |                 |  |            |  |                     |  |