



C-160208-E

REVISIONS				
LTR	DESCRIPTION	DATE	DWN	APVD
G1	REVISED PER-ECO-09-022178	21SEP09	KK	AEG
G2	REVISED PER ECR-17-013411	15SEP2017	BDA	FV



2 OBSOLETE

1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

1-160208-2	STEEL	NICKEL
1-160208-4	PHOS. BRONZE	TIN
4-160208-0	STEEL	NICKEL WEL. CO.

* REELED WITH PAPER.
160208-7 SUITABLE FOR AMP-D-MATOR APPLICATION (12000 PLS. PER REEL)

CUSTOMER COPY FOR REFERENCE ONLY

©1966 BY AMP-HOLLAND N.V. ALL RIGHTS RESERVED AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

STE TE Connectivity

WIRE RANGE	SHIELD RANGE	FIRST USED
25-40 AWG	23-25 P.M.M.	

SCALE	LOC	SIZE	NO
4:1	H	A	C-160208-E

REV
G2

NAME
PIN RECEPTACLE

DIMENSIONS IN MM DO NOT SCALE PRINT

ORDER NO.	MATERIAL	PLATING
DE P. BOND. 28/ DATE DE 12-86		
CHK DATE APP 4-87		

AMP 1282