


HBL2710 -- Twist-Lock Receptacle




3P4W, 30A 125/250V, L14-30R, Black Nylon Face



Product Specifications

| | |
|-----------------------------------|---|
| Product Type |  Twist-Lock Devices |
| Product Item | Single Receptacle |
| Wiring Scheme | 3 Pole, 4 Wire Grounding |
| Amperage | 30A |
| Voltage | 125/250V AC |
| NEMA Configuration | L14-30R |
| Item Style | Standard |
| Device Color | Black |
| Horsepower | 2 |
| Terminal Retainer Material | Clear polycarbonate |
| Terminal Clamp Material | .040" (1.0)Brass |
| Terminal Screw Material | #10-32 Bronze (White finish on neutral screw when used) |

| | |
|---|--|
| Ground Screw Material | #10-32 Bronze (Green) |
| Contact Spring Material | .040" Brass |
| Mounting Screw Material | Steel, zinc plated |
| Cover (Top) Material | Black Nylon |
| Base Material | Nylon Polyester |
| Ground Contact Material | .040" Brass |
| Bridge (Mounting Strap) Material | .050" Brass |
| Back Plate Material | .040" Brass |
| Rivet Material | Brass |
| Auto Ground Clip Material | Stainless Steel |
| Ratings | Molded into face. |
| Catalog No. | Marked onto body |
| Dielectric Voltage Withstand | 2,000V minimum |
| Current Interrupting | Certified for current interrupting at full rated current. |
| Temperature Rise | Max 30 C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75. |
| Terminal Accommodation | 30A-#10AWG |
| Terminal Identification | Terminals identified in accordance with UL 498 (X, Y, Z, White, Green) |
| Flammability | HB or better per UL 94 or CSA 22.2 No. 0.6 |
| Operating Temperatures | Maximum Continuous 75 C Minimum -40 C (w/o impact) |
| Listings | FED SPEC UL/CSA |
| Catalog Page | Click here for catalog page B40 |
| Brochures | Click here for product brochure |
| Hubbellnet | Click here for Hubbellnet |
| Catalog Section | Click here for Section-B |
| UPC Number | 78358523608 |
| Weight in LBs | 0.3 |



TWIST-LOCK® Devices
3 Pole, 4 Wire Grounding
30 Ampere, 125/250 Volts and 3Ø 250 Volts
Receptacles, INSULGRIP® Connector Bodies, Flanged Devices and Plugs



NEMA L14-30R
30A 125/250V
UL/CSA
2 (2) HP

NEMA L15-30R
30A 3Ø 250V AC
UL/CSA
3 HP

Single Flush Receptacles, Back and Side Wired

| Description | Catalog Numbers |
|-------------------------------------|-----------------|
| Black nylon face. | HBL2710 HBL2720 |
| Isolated ground, orange nylon face. | IG2710 IG2720 |

Insulgrip Connector Bodies IP20 SUITABILITY

| Description | Catalog Numbers |
|------------------------------------|---------------------|
| Black and white nylon. | HBL2713 HBL2723 |
| Corrosion resistant, yellow nylon. | HBL27CM13 HBL27CM23 |

Note: Cord clamp range .35"-1.15" (9-29).

Insulgrip Flanged Receptacles

| Description | Catalog Numbers |
|---------------------------|-----------------|
| Nylon casing, back wired. | HBL2716 HBL2726 |



NEMA L14-30P
30A 125/250V
UL/CSA
2 (2) HP

NEMA L15-30P
30A 3Ø 250V AC
UL/CSA
3 HP

Insulgrip Plugs IP20 SUITABILITY

| Description | Catalog Numbers |
|------------------------------------|---------------------|
| Black and white nylon. | HBL2711 HBL2721 |
| Corrosion resistant, yellow nylon. | HBL27CM11 HBL27CM21 |

*Notes: Cord clamp range .35"-1.15" (9-29).
See page B-73 for Add-A-Shroud™ kit.*

Insulgrip Flanged Inlets

| Description | Catalog Numbers |
|---------------------------|-----------------|
| Nylon casing, back wired. | HBL2715 HBL2725 |

*Notes: HP ratings not in parentheses are phase to phase.
HP rating in parentheses is phase to neutral.
Only receptacles and plugs are HP rated.
See pages B-70 and B-71 for accessories.
For technical information see page B-83.
See page B-63 for switched enclosure.*