

HF41F

SUBMINIATURE POWER RELAY



File No.: E133481



File No.: 40020043



File No.: CQC17002175724



Features

- Slim size (width 5mm)
- 6A switching capability 4kV dielectric strength (between coil and contacts)
- Surge voltage up to 6kV (between coil and contacts)
- Meeting VDE 0700, 0631 reinforce insulation
- High sensitive: Approx.170mW
- Sockets available
- 1 Form A and 1 Form C configurations

CONTACT DATA

Contact arrangement	1A, 1C
Contact resistance ¹⁾	No gold plated:100mΩ max. (at 1A 6VDC) Gold plated: 30mΩ max. (at 1A 6VDC)
Contact material	AgSnO ₂ , AgNi
Contact rating (Res. load)	6A 250VAC / 30VDC
Max. switching voltage	400VAC / 300VDC
Max. switching current	6A
Max. switching power	1500VA / 180W
Mechanical endurance	1 x 10 ⁷ ops
Electrical endurance	H type: 6 x 10 ⁴ ops (6A 250VAC/30VDC, Resistive load, AgNi, at 85°C, 1s on 9s off) Z type: 3 x 10 ⁴ ops (NO, 6A 250VAC/30VDC, Resistive load, AgNi, at 85°C, 1s on 9s off) 1 x 10 ⁴ ops (NC, 6A 250VAC/30VDC, Resistive load, AgNi, at 85°C, 1s on 9s off)

Notes: 1) The data shown above are initial values.

CHARACTERISTICS

Insulation resistance		1000MΩ (at 500VDC)
Dielectric strength	Between coil & contacts	4000VAC 1 min
	Between open contacts	1000VAC 1 min
Operate time (at rated.volt.)		8ms max.
Release time (at rated.volt.)		4ms max.
Shock resistance*1)	Functional	49m/s ²
	Destructive	980m/s ²
Vibration resistance*1)		10Hz to 55Hz 1mm DA
Humidity		5% to 85% RH
Ambient temperature		-40°C to 85°C
Termination		PCB
Unit weight		Approx. 5g
Construction		Plastic sealed, Flux proofed

- Notes: 1) *Index is that of relay without socket and is not in relay length direction.
2) The data shown above are initial values.
3) Please find coil temperature curve in the characteristic curves below.
4) Please do not install a SPDT(1 Form C) type relay on either of the smallest sides or facing downward.
5) UL insulation system: Class A.

COIL

Coil power	5VDC to 24VDC: Approx. 170mW 48VDC, 60VDC: Approx. 210mW
------------	---

COIL DATA

at 23°C

Nominal Voltage VDC	Pick-up Voltage VDC max. ²⁾	Drop-out Voltage VDC min. ²⁾	Max. Voltage VDC ³⁾	Coil Resistance Ω
5	3.75	0.25	7.5	147 x (1±10%)
6	4.50	0.30	9.0	212 x (1±10%)
9	6.75	0.45	13.5	476 x (1±10%)
12	9.00	0.60	18	848 x (1±10%)
18	13.5	0.90	27	1906 x (1±15%)
24	18.0	1.20	36	3390 x (1±15%)
48 ⁴⁾	36.0	2.40	72	10600 x (1±15%)
60 ⁴⁾	45.0	3.00	90	16600 x (1±15%)

- Notes: 1) When require pick-up voltage ≤ 70% nominal voltage, special order allowed.
2) The data shown above are initial values.
3) Maximum voltage refers to the maximum voltage which relay coil could endure in a short period of time.
4) For products with rated voltage ≥ 48V, measures should be taken to prevent coil overvoltage in order to protect coil in test and application (eg. Connect diodes in parallel).

SAFETY APPROVAL RATINGS

UL/CUL	6A 30VDC at 85°C 6A 277VAC at 85°C R300 B300
VDE	6A 30VDC at 85°C 6A 250VAC at 85°C

- Notes: 1) All values unspecified are at room temperature.
2) Only typical loads are listed above. Other load specifications can be available upon request.



HONGFA RELAY

ISO9001, ISO/TS16949, ISO14001, OHSAS18001, IECQ QC 080000 CERTIFIED

2020 Rev. 1.01

ORDERING INFORMATION									
Type	HF41F /		12	-H	8	S	T	G	(XXX)
Coil voltage	5, 6, 9, 12, 18, 24, 48, 60VDC								
Contact arrangement	H: 1 Form A		Z: 1 Form C						
Version ¹⁾	8: Flat pack version		Nil: Vertical version						
Construction ²⁾³⁾	S: Plastic sealed		Nil: Flux proofed						
Contact material	T: AgSnO ₂		Nil: AgNi						
Contact plating ⁴⁾	G: Gold plated		Nil: No gold plated						
Special code ⁵⁾	XXX: Customer special requirement				Nil: Standard				

2) We recommend flux proofed types for a clean environment (free from contaminations like H_2S , SO_2 , NO_2 , dust, etc.). We suggest to choose plastic sealed types and validate it in real application for an unclean environment (with contaminations like H_2S , SO_2 , NO_2 , dust, etc.).

4) For gold plated type, the min. switching current and min. switching voltage is 10mA 5VDC.

6) Standard tube packing length is 550mm. Any special requirement needed, please contact us for more details.

OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT

Outline Dimensions

1 Form C

Technical drawing of a mechanical part with dimensions:

- Overall width: 28
- Overall height: 15
- Top flange thickness: 0.5
- Bottom flange thickness: 0.5
- Distance from left edge to first hole center: 0.5
- Distance between hole centers: 0.5
- Distance from right edge to last hole center: 0.5
- Distance from left edge to first hole center: 0.9
- Distance from first hole center to second hole center: 3.78
- Distance from second hole center to third hole center: 16.38
- Distance from third hole center to fourth hole center: 5.04
- Distance from fourth hole center to right edge: 1
- Distance from fifth hole center to right edge: 1
- Distance from bottom edge to hole center: 3.5
- Distance from bottom edge to hole center: 5

[illegible]

Technical drawing of a mechanical part, showing two views: a front view (top) and a side view (bottom).

Front View Dimensions:

- Overall width: 28
- Overall height: 3.0
- Left side features:
 - Top flange width: 0.5
 - Bottom flange width: 0.9
 - Distance from left edge to first vertical feature: 0.5
 - Distance between first and second vertical features: 3.78
- Right side features:
 - Distance from second vertical feature to centerline: 1
 - Distance from centerline to third vertical feature: 1
 - Distance from third vertical feature to right edge: 5.04

Side View Dimensions:


- Overall width: 5
- Overall height: 15
- Top flange width: 0.2

OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT


Unit: mm

Outline Dimensions

1 Form A
Special code: (414)




1 Form C




PCB Layout (Bottom view)

1 Form A



Vertical version





1 Form C



Flat pack version




Special code: (414)



Wiring Diagram (Bottom view)

1 Form A




1 Form C




Remark: 1) In case of no tolerance shown in outline dimension: outline dimension $\leq 1\text{mm}$, tolerance should be $\pm 0.2\text{mm}$; outline dimension $> 1\text{mm}$ and $\leq 5\text{mm}$, tolerance should be $\pm 0.3\text{mm}$; outline dimension $> 5\text{mm}$, tolerance should be $\pm 0.4\text{mm}$.
2) The tolerance without indicating for PCB layouts is always $\pm 0.1\text{mm}$.

CHARACTERISTIC CURVES

MAXIMUM SWITCHING POWER




ENDURANCE CURVE



Test conditions:

NO, AgNi, Resistive load, 250VAC,
Flux proofed, Room temp., the typical
value of test 1s on 9s off.


COIL TEMPERATURE RISE



Test conditions:


6A 85°C
(Typical curve of 24VDC standard type)

LOAD SWITCHING CAPACITY CURVE



Test conditions: NO, Room temp.

BREAKING CAPACITY TRIP CURVE



Test conditions:

Room temp., Plastic sealed, 1s on 9s off.

Disclaimer

The specification is for reference only. See to "Terminology and Guidelines" for more information. Specifications subject to change without notice. We could not evaluate all the performance and all the parameters for every possible application. Thus the user should be in a right position to choose the suitable product for their own application. If there is any query, please contact Hongfa for the technical service. However, it is the user's responsibility to determine which product should be used only.

© Xiamen Hongfa Electroacoustic Co., Ltd. All rights of Hongfa are reserved.