




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
-	-		B1	REVISED AS PER ECO-15-001798	02SEP2014	VNB
			B2	REVISED PER PCN E-20-000705	28JAN2020	MK
			C	REVISED PER PCN-24-219560	30AUG2024	CO
			D	REVISED PER PCN-25-233530	12DEC2024	RK



7 DATE CODE: IDENTIFIES THE YEAR ,MONTH,DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS.(14=2014)
MONTH: THIRD DIGIT,EXCLUDING I.A=JAN., B=FEB., C=MARCH...(K=OCT.)
DAY: FOURTH AND FIFTH DIGIT (14=14TH DAY)
HOUR: SIXTH AND SEVENTH DIGIT (11=11AM)

6 MATERIAL:
RECEPTACLE HOUSING: 6061-T6 ALUMINUM ALLOY,
GROMMET: SILICONE VMQ (RED),
RETAINER RING: PA66 GF10.

5. THIS PART MATES WITH HD36-24-XXXP/SX-XXXX


4. PART NUMBER INFO: XX= ARRANGEMENT: X= SEAL TYPE

3 TOTAL DIM. WITH EXTENDED WIRE SEAL (WITH CONTACTS
#4 OR #8 ONLY) = 1.870±.050 [47.50±1.27].

2. FOR ARRANGEMENT OF CONTACT LOCATION
SEE ENVELOPE DRAWING 0425-014-2400.

1. CONSULT THE FACTORY FOR ELECTRICAL AND MATERIAL SPECIFICATIONS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN VIJETH BHARADWAJ 30OCT2014	 TE Connectivity						
DIMENSIONS: INCHES[mm]		CHK I. GRANTCHAROVA 31OCT2014	NAME RECEPTACLE CONNECTOR SHELL SIZE 24 BAYONET COUPLING HD30 SERIES						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. MEYER 31OCT2014							
	0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±.010 [±.254] 4 PLC ±- ANGLES ±0° 30' 0"	PRODUCT SPEC 108-151014							
	MATERIAL	FINISH -	APPLICATION SPEC 114-151014	SIZE A3	CAGE CODE -	DRAWING NO G-HD34-24-XXP/SX	RESTRICTED TO -		
			Customer Drawing			SCALE NONE	SHEET 1	OF 1	REV D