


Technical specifications

Features

- Extremely small size (only 8,2x2,7x6,2mm)
- Specially-conceived for low switching currents and voltages
- Available with or without integrated auxiliary actuator
- Solder connection or use lying or standing on a circuit board

Dimensions in mm



Auxiliary actuator options


Auxiliary actuator	Operating force max. (cN)	Max. pretravel (mm)	Min. overtravel (mm)	Differential travel max. (mm)	Max. rest position (mm)	Operating point (mm)
Without auxiliary actuator	90	0,35	0,1	0,07	6,2	$5,6 \pm 0,15$
With auxiliary actuator	50	1,3	0,3	0,6	8,5	$6,7 \pm 0,5$

Preferred parts

Order code	Electrical rating	Terminals	Auxiliary actuator	Operating force (cN)	Operating point (mm)	Max. pretravel (mm)	Min. overtravel (mm)	Differential travel max. (mm)
DH2C-B1AA	5–500mA, 30VDC	Solder terminal straight, 1,3x3,1 mm	–	90	$5,6 \pm 0,15$	0,35	0,1	0,07
DH2C-B1PA	5–500mA, 30VDC	Solder terminal straight, 1,3x3,1 mm	Plastic, straight	50	$6,7 \pm 0,5$	1,3	0,3	0,6
DH2C-C4AA	5–500mA, 30VDC	PCB terminal straight, 0,64x3,1 mm	–	90	$5,6 \pm 0,15$	0,35	0,1	0,07
DH2C-C5AA	5–500mA, 30VDC	PCB terminal right, 0,64x3,1 mm	–	90	$5,6 \pm 0,15$	0,35	0,1	0,07
DH2C-C6AA	5–500mA, 30VDC	PCB terminal left, 0,64x3,1 mm	–	90	$5,6 \pm 0,15$	0,35	0,1	0,07

Terminals


Solder terminal



Drilling pattern



PCB terminal straight



PCB terminal
RH-side



LH-side



Auxiliary actuator options (plastic)

