



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : DDM-200-028 REV: 1.0

2.0" 5*7 Dot Matrix Displays

MODEL NO : ELM-2002SYGWA/S530-E1 ECN : Page: 1/5

■ Features :

- Large emitting dot 0.2" diameter.
- Low power/high brightness.

■ Applications:

- Instrument panels
- Digital read out display

■ Description :

- The ELM-2002 series are a large emitting area(5.0mm diameter)LED sources configured in a 35 dots 5*7 matrix array.
- These device is made with white dots and gray surface.

PART NO	CHIP		C.C. or C.A.
	Material	Emitted Color	
ELM-2002SYGWA/S530-E1	AlGaInP	Super Yellow Green	C.A.

OFFICE : NO. 25,Lane 76,Sec.3, Chung Yang Rd., Tucheng 236, Taipei, Taiwan, R.O.C.

TEL : 886-2-2267-2000,2267-9936

FAX : 886-2-2267-6244,22676189,22676306


<http://www.everlight.com>



2.0" 5*7 Dot Matrix Displays

MODEL NO : ELM-2002SYGWA/S530-E1 ECN : Page: 2/5

■ Package Dimension:



■ NOTES:

- 1.All dimensions are millimeters , tolerance is 0.25mm unless otherwise noted.
 - 2.Above specification may be changed without notice.
- Supplier will reserve authority on material change for above specification.



2.0" 5*7 Dot Matrix Displays

MODEL NO : ELM-2002SYGWA/S530-E1 ECN : Page: 3/5

■ Absolute maximum ratings at Ta = 25°C :

Parameter	Symbol	Rating	Unit
Reverse Voltage	Vr	5	V
Forward Current	If	25	mA
Operating Temperature	Topr	-40 to +85	°C
Storage Temperature	Tstg	-40 to +100	°C
Soldering Temperature	Tsol	260 ± 5	°C
Electrostatic Discharge	ESD	2000	V
Power Dissipation	Pd	60	mW
Peak Forward Current(Duty 1/10 @ 1KHZ)	If(Peak)	160	mA

■ Electronic optical characteristics :

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Condition
Luminous Intensity	Iv	0.75	1.7	----	mcd	If=2mA
		4.0	11.2			If=10mA
Peak Wavelength	λ_p	----	575	----	nm	If=20mA
Dominant Wavelength	λ_d	----	573	----	nm	If=20mA
Spectrum Radiation Bandwidth	$\Delta\lambda$	----	20	----	nm	If=20mA
Forward Voltage	Vf	----	2.0	2.4	V	If=20mA
Reverse Current	Ir	----	----	10	μA	Vr=5V



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number DDM-200-028 REV: 1.0

2.0" 5*7 Dot Matrix Displays

MODEL NO ELM-2002SYGWA/S530-E ECN : Page: 4/5

Reliability test item and condition:

NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260℃ ± 5 ℃	5 SEC	76 PCS	0/1
2	Temperature Cycle	H : +85℃ 30min └ 5 min L : -55℃ 30min	50 CYCLE	76 PCS	0/1
3	Thermal Shock	H : +100℃ 5min └ 10 sec L : -10℃ 5min	50 CYCLE	76 PCS	0/1
4	High Temperature Storage	TEMP : 100℃	1000 HRS	76 PCS	0/1
5	Low Temperature Storage	TEMP : -55℃	1000 HRS	76 PCS	0/1
6	DC Operating Life	If = 10 mA	1000 HRS	76 PCS	0/1
7	High Temperature / High Humidity	85℃/85% RH	1000 HRS	76 PCS	0/1



2.0" 5*7 Dot Matrix Displays

MODEL NO: ELM-2002SYGWA/S530-E1 ECN: Page: 5/5

Typical Electro-Optical Characteristic Curves:

SYG

