




Technical drawing of a circular plate with the following dimensions and labels:

- Two large circular features on the left and right, each labeled $2-\phi 3.05 \pm 0.25$.
- A central cluster of 16 small circular features, labeled $\phi 1.09$.
- Overall width dimension: 24.99 .
- Distance from the left edge to the center of the left large feature: 5.00 .
- Distance from the center of the left large feature to the center of the right large feature: 24.99 .
- Distance from the center of the right large feature to the right edge: 1.95 .
- Distance from the center of the right large feature to the center of the rightmost small feature: 2.29 Typ.
- Distance from the center of the rightmost small feature to the center of the next small feature to its left: 0.25 .

Rated Current
2.5 amps per contact

Rated Voltage
300V DC

Withstanding Voltage
500V(r.m.s.) AC for 1 min

Insulation Resistance
More than 1000 Megohm
at 500V DC

Contact Resistance
15milliohm Max

Dielectric Strength
1000V for 1 min

REVISION	DATE	DESCRIPTION	DRAWN BY	DESIGNED BY	UNITS
A1	6/22/99	New Drawing	K. Wallace		mm [in]
A2	7/15/99	Rev. Dimensions	CHECKED BY	APPROVED BY	DATE
A3	11/10/00	ECO #99-193			6/22/99

D-Sub, 15 pin female, High Density
Compact Footprint (0.125")



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[K61-E15S-N30](#) [K61-E15S-N15](#) [K61-E15S-N](#)