

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

DIN 46247

LOC

A1

DIST

—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F3	REVISED PER ECO-11-005150	21MAR11	RK	HMR

1

MIN. 4.5 μm Sn OVER MIN. 2.5 μm Cu

2

MIN. 3μm Sn OVER MIN. 0.8μm Ni

3

PACKING: MAX. 3000 PIECES
PACKED INTO CARDBOARD BOX

4

RECOMMENDED DIA. FOR PCB: Ø1.4 -0.1

5

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

1

MIN. 4.5 μm Sn ÜBER MIN. 2.5 μm Cu

2

MIN. 3μm Sn ÜBER MIN. 0.8μm Ni

3

VERPACKUNG: MAX. 3000 TEILE
IN KARTON VERPACKT

4

EMPFOHLENE LEITERPLATTENBOHRUNG: Ø1.4 -0.1

5	OBSOLETE	0.8	1-726389-4	2	CuZn
		0.8	1-726389-3	MIN. 2 μm Ni	CuZn
5	OBSOLETE	0.8	1-726389-2	1	CuZn
		0.8	1-726389-1	PLAIN BLANK	CuZn
5	OBSOLETE	0.5	726389-3	MIN. 2 μm Ni	CuZn
		0.5	726389-2	1	CuZn
5	OBSOLETE	0.5	-726389-1	PLAIN BLANK	CuZn
		0.5	-726389-1	PLAIN BLANK	CuZn
		"A" DIMENSION MASS	ORDER NO. BESTELL-NR.	SURFACE OBERFLAECHE COLOUR/FARBE	MATERIAL

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.2

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL

SEE TABLE
SIEHE TABELLE

FINISH

SEE TABLE
SIEHE TABELLE

DWN WEITZEL 28-MAY-85

CHK PFEIFER 28-MAY-85

APVD MORITZ 02-JUL-85

PRODUCT SPEC

ACCORDING TO DIN 46244

APPLICATION SPEC

—

WEIGHT —

28-MAY-85

28-MAY-85

02-JUL-85

NAME

FASTON TAB 4.8
FLACHSTECKER 4.8

SIZE A3

CAGE CODE 00779

DRAWING NO C-726389

RESTRICTED TO —

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV F3

1470-19 (3/11)