

Pro/ENGINEER DRAWING

LOC	DIST	REVISIONS				
FT	0	P	LTR	DESCRIPTION	DATE	APVD
			-	SEE SHEET 1	-	-

- 1

MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
- 2

SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3


END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.
- 4

WIRE SIZE RANGE
SOLID WIRE: 0,03-2,5mm² (13AWG).
STRANDED WIRE: 0,03-1,5mm² (15AWG).
- 5

RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE N° E60677.
- 6

IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
- 7

NOT CUMULATIVE TOLERANCE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 20AUG2001	 TE Connectivity			
DIMENSIONS: mm 		CHK D. BIEVENOUR 20AUG2001				
		APVD D. BIEVENOUR 20AUG2001				
		PRODUCT SPEC -				
MATERIAL - FINISH -		APPLICATION SPEC -	NAME TERMINAL BLOCK PCB MOUNT TOP ENTRY WIRE, STACKING W/INTERLOCK, 5.08mm PITCH			
		WEIGHT -				
		CUSTOMER DRAWING		SIZE A3	CAGE CODE 00779	DRAWING NO C-282851
SCALE 3:1				SHEET 2	OF 2	REV C1