




	10	9	8	7	6	5	4	3	2	19203			
	MATERIAL NUMBER	ENGINEERING NUMBER	WIRE RANGE AWG	TAPED MATERIAL NUMBER	TAPED ENGINEERING NUMBER	T MAX	B MAX	F MIN	L MAX	E MIN	D1 MIN	D MAX	H NOMINAL
F	192030373	192030373	16-14	192030467	192030373T	.030/.75	.239/6.06	.252/6.40	.587/14.92	.173/4.40	.083/2.10	.138/3.50	1.184/30.07
	192030390	192030390	16-14	192030469	192030390T	.030/.75	.302/7.66	.307/7.80	.666/16.92	.173/4.40	.083/2.10	.138/3.50	1.184/30.07
	192030379	192030379	12-10	192030468	192030379T	.030/.75	.302/7.66	.307/7.80	.706/17.92	.213/5.40	.130/3.30	.185/4.70	1.235/31.37



NOTE(S):
1. MATERIAL: STEEL .016/0.40 THICK REF.
2. FINISH: NICKEL PLATED
3. PART IS ROHS COMPLIANT.
4. AMBIENT OPERATING TEMPERATURE UP TO 900 °F (483 °C).

ⓑ

ADDED OPERATING TEMP EC NO: ETC2007-0297 2007/03/13 DRAWN: EHLE 2007/03/13 CHKD: JMACNEIL 2007/03/14 APPR: JMACNEIL	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY	DATE	TITLE KRIMPTITE QUICK DISCONNECT, STEEL, 900 DEG F (483 DEG C)	
			4 PLACES	± ---	± ---	ASAYDEH	05/12/02		
			3 PLACES	± ---	± ---	CHECKED BY	DATE		
			2 PLACES	± ---	± ---	R DEROSS	05/12/02		
			1 PLACE	± ---	± ---	APPROVED BY	DATE		
			ANGULAR ± ---°		R DEROSS	05/12/02	 MOLEX INCORPORATED		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE CHART			DOCUMENT NO. SD-19203-025	
SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								