




LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			T1	REVISED PER ECO-11-004835	11MAR11	RK	HMR



SECTION A-A

- 1 HOUSING FULLY LOADED WITH CONTACTS.
- 2 NUMBER ON CONTACT INDICATES WIRE RANGE.
- 3 CONTACT INSULATION RANGE: .060 MAXIMUM O.D.
- 4 CONTACTS PLATED GOLD PLATED FOR LENGTH OF .150 MIN FROM MATING END, .000030 MIN GOLD IN MATED AREA. .000100-.000200 BRIGHT TIN OR BRIGHT IN TIN-LEAD AREA SHOWN. .000050 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 5 CONTACTS PLATED GOLD PLATED FOR LENGTH OF .150 MIN FROM MATING END, GOLD FLASH IN MATED AREA. .000100-.000200 BRIGHT TIN OR BRIGHT IN TIN-LEAD AREA SHOWN. .000030 NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 6 CONTACTS PLATED .000100-.000200 THICK BRIGHT TIN OR BRIGHT TIN-LEAD WITH .000050 THICK NICKEL UNDERPLATE BOTH OVER ENTIRE CONTACT.
- 7 CONTACTS GOLD PLATED FOR A LENGTH OF .150 MIN FROM MATING END, .000030 MIN GOLD IN MATED AREA, .000100-.000200 MATTE TIN IN AREA SHOWN, ALL OVER .000050 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- OR
- CONTACTS GOLD PLATED FOR A LENGTH OF .150 MIN FROM MATING END, GOLD FLASH OVER PALLADIUM-NICKEL, .000030 MIN TOTAL IN MATED AREA, .000100-.000200 MATTE TIN IN AREA SHOWN, ALL OVER .000050 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 8 CONTACTS PLATED GOLD FLASH FOR A LENGTH OF .150 MIN FROM MATING END, .000100-.000200 MATTE TIN IN AREA SHOWN, ALL OVER .000030 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 9 HOUSING: BLACK THERMOPLASTIC 94V-0 RATED. CONTACTS: PHOSPHOR BRONZE.

			2	#22-26	1-745203-1
	OBSOLETE		3	#20-22	1-745203-0
			2	#22-26	745203-9
	OBSOLETE		1	#26-30	745203-8
	OBSOLETE		1	#26-30	745203-7
SUPD BY 745203-3			3	#20-22	745203-6
	OBSOLETE		2	#22-26	745203-5
	OBSOLETE		1	#26-30	745203-4
	OBSOLETE		3	#20-22	745203-3
	OBSOLETE		2	#22-26	745203-2
	OBSOLETE		1	#26-30	745203-1
		FINISH		AWG WIRE RANGE	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - DOCKS 11-17-04	TE Connectivity	
DIMENSIONS: INCHES		CHK J. GERACE 11-17-04	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 2°		APVD M. WALMSLEY 11-17-04	PRODUCT SPEC 108-40011	
MATERIAL 9		APPLICATION SPEC 114-40002	SIZE A1	
SEE TABLE		WEIGHT -	CAGE CODE 00779	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1
		REV T1		