


M57788M

430-450MHz, 12.5V, 45W, FM MOBILE RADIO


OUTLINE DRAWING

Dimensions in mm



H3

BLOCK DIAGRAM



PIN :

- ① Pin : RF INPUT
- ② Vcc1 : 1st. DC SUPPLY
- ③ Vcc2 : 2nd. DC SUPPLY
- ④ Vcc3 : 3rd. DC SUPPLY
- ⑤ Po : RF OUTPUT
- ⑥ GND : FIN

ABSOLUTE MAXIMUM RATINGS (Tc = 25 °C unless otherwise noted)

Symbol	Parameter	Conditions	Ratings	Unit
Vcc1	Supply voltage		16	V
Vcc2,3			17	V
Icc	Total current		12	A
Pin(max)	Input power	ZG = ZL = 50 Ω	0.6	W
Po(max)	Output power	ZG = ZL = 50 Ω	50	W
Tc(OP)	Operation case temperature		- 30 to 110	°C
Tstg	Storage temperature		- 40 to 110	°C

Note. Above parameters are guaranteed independently.


ELECTRICAL CHARACTERISTICS (Tc = 25 °C unless otherwise noted)

Symbol	Parameter	Test conditions	Limits		Unit
			Min	Max	
f	Frequency range	Pin = 0.4W Vcc = 13.5V ZG = ZL = 50 Ω	430	450	MHz
Po	Output power		45		W
η T	Total efficiency		40		%
2fo	2nd. harmonic			- 30	dBc
3fo	3rd. harmonic			- 30	dBc
ρin	Input VSWR			3.0	-
-	Load VSWR tolerance	Vcc = 15.2V, Po = 45W (Pin : controlled) Load VSWR=8.8:1(All phase), ZG = 50 Ω	No degradation or destroy		-


Note. Above parameters, ratings, limits and conditions are subject to change.

TYPICAL PERFORMANCE DATA


OUTPUT POWER, TOTAL EFFICIENCY,
INPUT VSWR VS. FREQUENCY CHARACTERISTICS




OUTPUT POWER, EACH CURRENT
VS. INPUT POWER CHARACTERISTICS




OUTPUT POWER, EACH CURRENT
VS. INPUT POWER CHARACTERISTICS



OUTPUT POWER, EACH CURRENT VS.
1st SUPPLY VOLTAGE CHARACTERISTICS



OUTPUT POWER, EACH CURRENT VS.
1st SUPPLY VOLTAGE CHARACTERISTICS



OUTPUT POWER, EACH CURRENT
VS. SUPPLY VOLTAGE CHARACTERISTICS

