

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
1	2		A	ES00-0102-00	11OCT00	J.C.	J.L.
			B	ES00-0007-02	24JAN02	A.H.	J.L.
			C	ES00-0133-03	08JAN04	J.L.	J.L.
			D	ET00-0026-05	29MAR05	A.V.	G.T.
			D1	ECO-09-025699	11JAN10	KK	AEG

SECTION C-C

SECTION D-D

SCALE 6:1

1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

GUION DASH	MATERIAL	ACABADO FINISH
-5	ACERO STEEL	PRENIQUELADO PRENI
-4	BRONCE BRONZE	-
-3	LATON BRASS	PRESTAÑADO PRETIN
-2	LATON BRASS	ESTANADO TIN PLATED
-1	LATON BRASS	-

1 PARA LENGÜETA CON AGUJERO DE 0,8 mm DE ESPESOR
FOR TAB WITH HOLE OF 0.8 mm THICKNESS

1 GAMA DE HILO: 0,3 - 0,8 mm² ; GAMA DE AISLANTE: 2,3 - 3,3 mm
1 WIRE RANGE: 0.3 - 0.8 mm² ; ISULATION RANGE: 2.3 - 3.3 mm

DIMENSIONS: MEDIDAS, mm	DWN /DIB	30SEP97	MATERIAL	TABLE	FINISH ACABADO	TABLE
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCIAS POR OMISION 0 PLC /LUG ±0.4 1 PLC /LUG ±0.3 2 PLC /LUG ±0.13 3 PLC /LUG ±0.13 4 PLC /LUG ±0.001 ANGLES /ANGULOS ±-	CHK /COMP	30.9.97	AMP Amp Española Barcelona. Spain.			
	APVD /APR	11OCT00	RECEPTACULO FASTON 6,35 FASTON RECEPTACLE 6.35			
	PRODUCT SPEC ESPEC PRODUCTO	108-22021 -1to-4 108-22080 -5	NAME TITULO			
	APPLICATION SPEC ESPEC APLICACION	114-2036	SIZE TAM CAGE CODE CODIGO DRAWING NO PLANO NO RESTRICTED TO RESTRINGIDO A			
WEIGHT PESO		A4 00779		C=336235		REV D1

CUSTOMER DRAWING /PLANO DE CLIENTE

SCALE ESCALA 3:1 SHEET HOJA 1 OF DE 1