

## 8 outlet, 12ft cord, 3840 Joules, Remote on/off switch, All-metal housing - Isobar Surge Suppressor

MODEL NUMBER: **IB8RM**



### Description

For more than 20 years, America's leading companies have trusted Tripp Lite's Isobar Premium surge and noise suppressors to protect sensitive computer, networking and telecom equipment. With more than 18 million satisfied customers, the Isobar remains the world's #1 selling premium surge suppressor. Loaded with a generous combination of high quality components, near indestructible all-metal case and unique noise filtration system, the Isobar offers the highest level of protection attainable in a multi-outlet strip. Robust surge suppression circuits with sine-wave tracking offer extreme levels of protection against the heaviest surge conditions exceeding IEEE 587 category A & B specifications and reducing 6,000V test surges to harmless levels under 35 volts. Isobar's unique protection system combines large toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors into exclusive isolated filter banks that remove EMI/RFI interference, even noise generated by other pieces of connected equipment. IB8RM offers 8 outlets arranged in four filter banks to prevent system crashes, reboots and performance problems common as noisy system peripherals are powered off and on. Surge suppression rated at 3840 joules/97,000 amps offers network-grade protection. Widely spaced NEMA 5-15 outlets accommodate up to 4 large transformer plugs without blocking outlets. Unique mountable remote switch at the end of a 9 foot cord allows convenient power switching of desktop computers and peripherals without reaching under desks or workbenches. 12 foot AC line cord with space-saving angled input plug and keyhole mounting tabs.

PLUG/OUTLETS: Input: NEMA 5-15P/Output: 8 NEMA 5-15R/12-ft. AC line cord/Remote power switch with 9 foot cord

ELECTRICAL: 120V AC, 50/60Hz (Requires NEMA 5-15R wall receptacle)

SUPPRESSION: AC: 140V RMS Clamping/3840 joules/97,000 amps

### Features

- Tripp Lite's ISOBAR is the world's #1 selling premium suppressor series with more than 18 million satisfied customers and a safety-tested history of 20+ years
- Robust surge suppression with sine-wave tracking protects against the heaviest of surge conditions, exceeding IEEE category A&B specifications and reducing 6,000V test surges to harmless levels less than 35 volts
- Multi-component suppression circuits combine toroidal chokes, ferrite rod-core inductors, HF/VHF capacitors and multiple layers of metal oxide varistors into exclusive isolated filter banks that remove EMI/RFI interference, even noise from other pieces of connected equipment

### Highlights

- 8 outlets / 12-ft. cord
- 3840 joule rating
- Remote on/off switch on a 9-ft. cord
- All metal housing
- Isolated filter banks
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

### Applications

- Ideal for premium protection and convenient power off/on control of personal computers with peripherals, network and CAD/CAM/CAE workstations, internetworking accessories, telecommunications systems, point of sale equipment, audio/video and home theater systems in any home, office or industrial application.

### Package Includes

- IB8RM Surge Suppressor
- Instruction manual with warranty information



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

- 8 outlets arranged in four filter banks prevent system crashes, reboots and performance problems common as noisy peripherals are powered off and on
- Network grade surge suppression rated at 3840 joules/97,000 amps
- Widely spaced outlets accommodate up to 4 large transformer plugs without blocking outlets
- Lighted power switch with integrated 12 amp circuit breaker offers power control and overload protection
- 12 foot AC line cord with space-saving angled input plug
- Keyhole mounting tabs for installation in a variety of application
- 120V AC, 50/60Hz electrical compatibility
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OVERVIEW	
Intended Application	Home/Office; Computer Networks
Style	Strip
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1440
Circuit Breaker (amps)	12
Outlet Quantity / Type	8 NEMA 5-15R
Number of Outlets	8
Transformer Accommodation	Supports up to 4 large transformer plug accessories without covering remaining outlets
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P input plug
Input Plug Features	Space-saving right angle input plug
Input Cord Length (ft.)	12
Input Cord Length (m)	3.7
Voltage Compatibility (VAC)	120
Maximum Surge Amps	150000
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and mountable two position illuminated on/off power switch at the end of a 9 foot cable
SURGE / NOISE SUPPRESSION	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

AC Suppression Joule Rating	3840
AC Suppression Response Time	NM = 0 ns. CM = <1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	140V
AC Suppression Surge Current Rating	97,000 amps (36,000 NM / 61,000 CM)
AC Suppression Components Used	Metal oxide varistors, toroidal balanced chokes, ferrite rod-core inductors and VHF capacitors.
Safe Thermal Fusing	Prevents unsafe conditions during extreme extended over-voltages and catastrophic occurrences
UL1449 Let Through Rating	330V
IEEE587 Cat. A Ringwave Let-Through	Less than 35 volts
EMI / RFI Filtering	40-80 dB
Isolated Filter Banks	Unique isolated filter bank design offers additional filtering between each duplex pair of outlets on the strip to prevent electrical noise interference between connected loads. Includes 4 filter banks.
Immunity	Conforms to IEE 587 / ANSI C62.41

#### DATALINE SURGE SUPPRESSION

Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No

#### PHYSICAL

Unit Dimensions (hwd / in.)	2.5 x 9 x 3.5
Unit Dimensions (hwd / cm)	6.4 x 22.9 x 8.9
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Metal end caps and remote power switch are fitted with keyhole mounting tabs for desk or wallmount installation
Housing Color	Light Gray
Receptacle Color	Black
Color (AC Line Cord)	Light Gray
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 39.45mm; Distance between vertical outlets = 38.66mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal tabs = 210.79mm; Distance between vertical tabs = 58.17mm

#### SPECIAL FEATURES

Right-Angle Plug	Yes
------------------	-----

#### CERTIFICATIONS



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3rd Edition by ETL
cUL / CSA (Canada)	Approved for Canada by ETL
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 <a href="#">Ultimate Lifetime Insurance</a>

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.