








PCB LAYOUT - COMPONENT VIEW



TECHNICAL CHARACTERISTICS

MATERIAL
 INSULATOR MATERIAL: PBT
 FLAMMABILITY RATING UL94-V0
 COLOR: BLACK
 CONTACT MATERIAL: COPPER ALLOY
 CONTACT TYPE: STAMPED
 CONTACT PLATING: SELECTIVE GOLD
 SHIELDING: BRONZE NI PLATED
 QUALITY CLASS: 500 MATING CYCLES

ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 °C UP TO 85 °C
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 CURRENT RATING: 1.5 A
 WORKING VOLTAGE: 120 VAC
 INSULATION RESISTANCE: >500 MΩ
 DIELECTRIC WITHSTANDING VOLTAGE: 1 000 VAC/MIN
 CONTACT RESISTANCE: 20 mΩ MAX

STANDARD
 CERTIFIED: E324776

SOLDERING
 JEDEC LEAD FREE WAVE SOLDERING PROCESS

PACKAGING
 TRAY

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15	 WÜRTH ELEKTRONIK		
G								
F	03-JAN-14	UL & TEMP UPDATE	QL					
E	20-AUG-13	DIM UPDATE	QL					
D	19-FEB-11	PLATING	GG					
C	07-OCT-09	UL STANDARD	JP	APPROVAL: RJ	UNIT: MM	DESCRIPTION: VERTICAL SHIELDED 8P8C REAR POST MODULAR JACK	SIZE	
B	06-OCT-09	CHARACTERISTIC	JP		SCALE:			
A	03-FEB-07	PDF	CH		SHEET: 1/1			WERI PART NO: 615 008 140 421
REV	DATE	FILE	BY		DRAW:			
A4								