

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED

© COPYRIGHT

By -

LOC	
-----	--

DIST

REVISIONS

P	17
---	----

--	--

DESCRIPTION

DATE _____

NAME	
------	--

MD


A1

REVISÉD PER ECO-11-004820

11MA





















RK H

MF



RECOMMENDED HOLE LAYOUT

1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
4. HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
5. FINISH: 0.000381[.000015] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.
6. FINISH: 0.000381[.000015] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL.

	101.19 [3.984]	99.06 [3.900]	39	40	9-146481-0
	98.65 [3.884]	96.52 [3.800]	38	39	8-146481-9
	96.11 [3.784]	93.98 [3.700]	37	38	8-146481-8
	93.57 [3.684]	91.44 [3.600]	36	37	8-146481-7
	91.03 [3.584]	88.90 [3.500]	35	36	8-146481-6
	88.49 [3.484]	86.36 [3.400]	34	35	8-146481-5
	85.95 [3.384]	83.82 [3.300]	33	34	8-146481-4
	83.41 [3.284]	81.28 [3.200]	32	33	8-146481-3
	80.87 [3.184]	78.74 [3.100]	31	32	8-146481-2
	78.33 [3.084]	76.20 [3.000]	30	31	8-146481-1
	75.79 [2.984]	73.66 [2.900]	29	30	8-146481-0
	73.25 [2.884]	71.12 [2.800]	28	29	7-146481-9
	70.71 [2.784]	68.58 [2.700]	27	28	7-146481-8
	68.17 [2.684]	66.04 [2.600]	26	27	7-146481-7
	65.63 [2.584]	63.50 [2.500]	25	26	7-146481-6
	63.09 [2.484]	60.96 [2.400]	24	25	7-146481-5
	60.55 [2.384]	58.42 [2.300]	23	24	7-146481-4
	58.01 [2.284]	55.88 [2.200]	22	23	7-146481-3
	55.47 [2.184]	53.34 [2.100]	21	22	7-146481-2
	52.93 [2.084]	50.80 [2.000]	20	21	7-146481-1
	50.39 [1.984]	48.26 [1.900]	19	20	7-146481-0
	47.85 [1.884]	45.72 [1.800]	18	19	6-146481-9
	45.31 [1.784]	43.18 [1.700]	17	18	6-146481-8
	42.77 [1.684]	40.64 [1.600]	16	17	6-146481-7
	40.23 [1.584]	38.10 [1.500]	15	16	6-146481-6
	37.69 [1.484]	35.56 [1.400]	14	15	6-146481-5
	35.15 [1.384]	33.02 [1.300]	13	14	6-146481-4
	32.61 [1.284]	30.48 [1.200]	12	13	6-146481-3
	30.07 [1.184]	27.94 [1.100]	11	12	6-146481-2
	27.53 [1.084]	25.40 [1.000]	10	11	6-146481-1
	24.99 [.984]	22.86 [.900]	9	10	6-146481-0
	22.45 [.884]	20.32 [.800]	8	9	5-146481-9
	19.91 [.784]	17.78 [.700]	7	8	5-146481-8
	17.37 [.684]	15.24 [.600]	6	7	5-146481-7
	14.83 [.584]	12.70 [.500]	5	6	5-146481-6
	12.29 [.484]	10.16 [.400]	4	5	5-146481-5
	9.75 [.384]	7.62 [.300]	3	4	5-146481-4
	7.21 [.284]	5.08 [.200]	2	3	5-146481-3
	4.67 [.184]	2.54 [.100]	1	2	5-146481-2
	2.13 [.084]	-	-	1	5-146481-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

5	101.19 [3.984]	99.06 [3.900]	39	40	4-146481-0
5	98.65 [3.884]	96.52 [3.800]	38	39	3-146481-9
5	96.11 [3.784]	93.98 [3.700]	37	38	3-146481-8
5	93.57 [3.684]	91.44 [3.600]	36	37	3-146481-7
5	91.03 [3.584]	88.90 [3.500]	35	36	3-146481-6
5	88.49 [3.484]	86.36 [3.400]	34	35	3-146481-5
5	85.95 [3.384]	83.82 [3.300]	33	34	3-146481-4
5	83.41 [3.284]	81.28 [3.200]	32	33	3-146481-3
5	80.87 [3.184]	78.74 [3.100]	31	32	3-146481-2
5	78.33 [3.084]	76.20 [3.000]	30	31	3-146481-1
5	75.79 [2.984]	73.66 [2.900]	29	30	3-146481-0
5	73.25 [2.884]	71.12 [2.800]	28	29	2-146481-9
5	70.71 [2.784]	68.58 [2.700]	27	28	2-146481-8
5	68.17 [2.684]	66.04 [2.600]	26	27	2-146481-7
5	65.63 [2.584]	63.50 [2.500]	25	26	2-146481-6
5	63.09 [2.484]	60.96 [2.400]	24	25	2-146481-5
5	60.55 [2.384]	58.42 [2.300]	23	24	2-146481-4
5	58.01 [2.284]	55.88 [2.200]	22	23	2-146481-3
5	55.47 [2.184]	53.34 [2.100]	21	22	2-146481-2
5	52.93 [2.084]	50.80 [2.000]	20	21	2-146481-1
5	50.39 [1.984]	48.26 [1.900]	19	20	2-146481-0
5	47.85 [1.884]	45.72 [1.800]	18	19	1-146481-9
5	45.31 [1.784]	43.18 [1.700]	17	18	1-146481-8
5	42.77 [1.684]	40.64 [1.600]	16	17	1-146481-7
5	40.23 [1.584]	38.10 [1.500]	15	16	1-146481-6
5	37.69 [1.484]	35.56 [1.400]	14	15	1-146481-5
5	35.15 [1.384]	33.02 [1.300]	13	14	1-146481-4
5	32.61 [1.284]	30.48 [1.200]	12	13	1-146481-3
5	30.07 [1.184]	27.94 [1.100]	11	12	1-146481-2
5	27.53 [1.084]	25.40 [1.000]	10	11	1-146481-1
5	24.99 [.984]	22.86 [.900]	9	10	1-146481-0
5	22.45 [.884]	20.32 [.800]	8	9	146481-9
5	19.91 [.784]	17.78 [.700]	7	8	146481-8
5	17.37 [.684]	15.24 [.600]	6	7	146481-7
5	14.83 [.584]	12.70 [.500]	5	6	146481-6
5	12.29 [.484]	10.16 [.400]	4	5	146481-5
5	9.75 [.384]	7.62 [.300]	3	4	146481-4
5	7.21 [.284]	5.08 [.200]	2	3	146481-3
5	4.67 [.184]	2.54 [.100]	1	2	146481-2
5	2.13 [.084]	-	-	1	146481-1
PLATING	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT

DWN 14-MAR-97
F BRANDBERG

E. BRANDBERG
CHK 14-MAR-97

G. DUBNICZKI

APVD 14-MAR-97
C. DUBNOZKI

G. DUBNICZKI
PRODUCT SPEC

PROJECT SITE

A 0000 0000 0 1 0000 00 0000 00 00 0 0000 0000 0000 0000

TE Connectivity

HEADER ASSEMBLY, MOD II,
STACKING, SINGLE ROW,
.025 SQ. POST. UNSHROUDED

SIZE	CAGE CODE	DRAWING NO.
------	-----------	-------------

SIZE	CASE CODE	DRAWING NO.
1/2"		1

RESTRICTED TO:

RESTRICTED TO

SCALE	SHEET	OF	REV
-------	-------	----	-----