





DDM/CAD
DRAWN
MAM
19 DEC 91
CHECK
TSM
12 DEC 91
CHECK
GLH
19 MAR 98
REVISES
B
81637
CO
20 OCT 92
MAM
A
073544
ISSUE
23
DRAWING
NUMBER
M
OP-AR141
REPLACES
PR-19685
RELEASE NO.



NOTES
1 - 8X MOUNTING SCREW HOLE, 10-32 UNF-2B THREADS X (.219) DEEP
2 - 8-32 UNC X (.219) TERMINAL SCREWS AND CUPWASHERS
3 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE



CHARACTERISTICS	ELECTRICAL DATA
OPERATING FORCE ----- 1/2 - 1 1/4 LB	CONTACT ARRANGEMENT S P D T
RELEASE FORCE ----- 1/4 LB MIN	L96
PRETRAVEL ----- .219 MAX 8°	15A 125, 250 OR 480 VAC
DIFFERENTIAL TRAVEL --- .007 MAX 1/4°	1/8HP 125 VAC, 1/4HP 250 VAC
DO NOT OVERTRAVEL MORE THAN --- 90°	1/2A 125 VDC, 1/4A 250 VDC
SWITCH - BASIC REPLACEMENT---BZ-2R-P4	



MASTER REDUCED
ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

MICRO SWITCH
a Honeywell Division

SWITCH - ENCLOSED

CATALOG LISTING
OP-AR141

FED. MFG. CODE 91929

THIRD ANGLE PROJECTION	
SCALE	FULL
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
ONE PLACE	(.0) ±.030
TWO PLACES	(.00) ±.015
THREE PLACES	(.000) ±.005
ANGLES	±
WEIGHT	