

DO NOT SCALE

DIMENSIONS IN mm

METRIC

THIRD ANGLE

PROJECTION



NOTES:

1 FOR USE ON MINIATURE APPLICATORS (LEFT-RIGHT FEED) AND
STANDARD APPLICATORS (RIGHT-LEFT FEED).





2 BRASS ACC. ASTM B36 ALLOY 250.

3 PH. BRONZE ACC. ASTM B103.


4 GAGE 0,74 MUST NOT ENTER, GAGE 0,58 MUST ENTER.

5 REELED WITH PAPER COVER.

6 UNLESS OTHERWISE SPECIFIED ALL TOLERANCES $\pm 0,4$ mm.



SECTION A-A



SECTION B-B

WIRE RANGE :
0,5-1,0 mm²
INSULATION RANGE :
1,4-2,3 DIA.

DIRECTION OFF TOP OF REEL



3/1	PH. BRONZE	PH. BRONZE 6XSn	160864-6
3/1	PH. BRONZE	PH. BRONZE 6XSn	160864-5
3/1	PRE-TINPLATED	PH. BRONZE 4XSn	160864-4
3/1	UNPLATED	PH. BRONZE 4XSn	160864-3
2/1	PRE-TINPLATED	BRASS	160864-2
2/1	UNPLATED	BRASS	160864-1
NOTES	FINISH	MATERIAL	PARTNUMBER

NOTES					CUSTOMER DRAWING		FOR REFERENCE ONLY WILL NOT BE UPDATED	
-	-	-	-	-				
-	-	-	-	-				
-	-	-	-	-	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION			
-	-	-	-	-	 TE Connectivity			
-	-	-	-	-	FORM			
D1	REVISED PER ECO-11-005150	RK	HMR	28MAR11	.110 SERIES FAST-IN-ON RECEPTACLE			
LTR.	REVISION RECORD		DR.	CHK.	DATE			
DR.	FILED IN	CHK.	APPROV.	DATE	DRG. NO.	REV. LTR.	SHEET	
DATE: 12-08-09	DATE:	-	DATE: 10-27-03		C-160864	D1	1 OF -	A3