



## OMNIDIRECTIONAL ANTENNAS FOR PCS/DCS AND WIRELESS LAN

Laird is world renowned for special purpose omnidirectional antenna design. Antennas are available for the 1.7 GHz DCS band through 5.8 GHz ISM band frequencies and can be suspension ceiling mounted, I-beam mounted or mast mounted.

## 2.4 GHz MONOPOLE OMNI

The Laird 2.4 GHz monopole antenna features a large backplane and is designed for applications with a very focused omnidirectional pattern where an in-building system is required. The monopole can be used to focus signal directly into an area where it is difficult to obtain any coverage.

## ANTENNA SELECTION CRITERIA

Prior to making an informed antenna selection, the following must be determined: what frequency range should the antenna cover? What gain is needed? If the exact gain is unknown, be able to describe the system that will use the antennas. For example, how large is the area? What obstructions are in the area (i.e. buildings, trees, shelves, walls, etc.)? Consider how the antenna will be mounted or at least what mount is preferable. With this information, a number of alternatives can be eliminated.


Currently, the most popular spread spectrum systems operate in the 900 MHz or the 2.4 GHz ranges, so these are basic spread options. Other data applications occur anywhere from 25 MHz to 5.9 GHz. Some antennas outside of the 900 MHz and 2.4 GHz ranges are also offered. Contact Laird to find your solution today!

## FEATURES


- Polycarbonate enclosures
- Available with ceiling mounts
- Plated copper laminated radiator
- Weatherproof designs with UltraLink pigtails
- Broadband performance
- DC grounded
- Omnidirectional performance

## MARKETS

- WiMAX



**S2403M**



**S2406BH**

Americas: +1.847.839.6907  
IAS-AmericasEastSales@lairdtech.com

Europe: +44.1628.858941  
IAS-EUSales@lairdtech.com

Asia: +86.21.5855.0827.127  
IAS-AsiaSales@lairdtech.com

[www.lairdtech.com](http://www.lairdtech.com)

| MODEL       | FREQUENCY<br>MHz | GAIN<br>dBi | BANDWIDTH<br>1.5:1<br>MHz | -3 dB<br>BEAMWIDTH<br>E-PLANE | HEIGHT<br>In<br>(cm) | WEIGHT<br>lb<br>(kg) | W/SUR<br>AREA<br>ft <sup>2</sup><br>(m <sup>2</sup> ) | W/SURVIVAL<br>mph<br>(kph) | POWER<br>(watts) | ENCLOSURE<br>MATERIAL     | MOUNT<br>STYLE   | MAST<br>DIAMETER<br>in<br>(cm) |
|-------------|------------------|-------------|---------------------------|-------------------------------|----------------------|----------------------|-------------------------------------------------------|----------------------------|------------------|---------------------------|------------------|--------------------------------|
| S5703BP5SMF | 5725-5875        | 3           | 150                       | 38°                           | 7<br>(17.8)          | 0.3<br>(0.14)        | 0.06<br>(0.006)                                       | 125<br>(200)               | 20               | Polycarbonate<br>Tube End |                  | 2<br>(5.1)                     |
| S5703BH7SMF | 5725-5875        | 3           | 150                       | 38°                           | 7<br>(17.8)          | 0.2<br>(0.1)         | 0.06<br>(0.006)                                       | 125<br>(200)               | 20               | Polycarbonate             | Ceiling          | N/A                            |
| S5153BP5SMF | 5150-5350        | 3           | 200                       | 38°                           | 7<br>(17.8)          | 0.2<br>(0.1)         | 0.06<br>(0.006)                                       | 125<br>(200)               | 20               | Polycarbonate<br>Tube End |                  | 2<br>(5.1)                     |
| S5153BH7SMF | 5150-5350        | 3           | 200                       | 38°                           | 7<br>(17.8)          | 0.2<br>(0.1)         | 0.06<br>(0.006)                                       | 125<br>(200)               | 20               | Polycarbonate             | Ceiling          | N/A                            |
| S5703M12NF  | 5725-5875        | 1           | 150                       | 60°                           | 1.5<br>(3.8)         | 0.4<br>(0.18)        | 0.02<br>(0.002)                                       | 125<br>(200)               | 20               | Polycarbonate             | Ceiling          | N/A                            |
| S2406BP7NF  | 2400-2500        | 6           | 100                       | 13°                           | 25<br>(63.5)         | 0.5<br>(0.23)        | 0.11<br>(0.01)                                        | 125<br>(200)               | 20               | Polycarbonate<br>Tube End |                  | 2<br>(5.1)                     |
| S2406BH12NF | 2400-2500        | 6           | 100                       | 13°                           | 25<br>(63.5)         | 0.5<br>(0.23)        | 0.11<br>(0.01)                                        | 80<br>(128)                | 20               | Polycarbonate<br>Tube End |                  | N/A                            |
| S2403M12NF  | 2400-2500        | 1           | 100                       | 60°                           | 2<br>(5.1)           | 0.5<br>(0.23)        | 0.02<br>(0.002)                                       | 125<br>(200)               | 50               | Polycarbonate             | Ceiling          | N/A                            |
| S2403BH12NF | 2400-2500        | 3           | 100                       | 38°                           | 11.5<br>(29.2)       | 0.31<br>(0.14)       | 0.08<br>(0.007)                                       | 125<br>(200)               | 50               | Polycarbonate             | Ceiling          | N/A                            |
| S2403BP12NF | 2400-2500        | 3           | 100                       | 38°                           | 11.5<br>(29.2)       | 0.41<br>(0.18)       | 0.08<br>(0.007)                                       | 125<br>(200)               | 50               | Polycarbonate<br>Tube End |                  | 2<br>(5.1)                     |
| S2400BH12NF | 2400-2500        | 0           | 100                       | 75°                           | 9<br>(22.9)          | 0.29<br>(0.13)       | 0.122<br>(0.011)                                      | 125<br>(200)               | 50               | Polycarbonate             | Ceiling          | N/A                            |
| S1805BNF    | 1850-1990        | 5           | 140                       | 16°                           | 31<br>(78.7 x 2.5)   | 2<br>(0.9)           | 0.14<br>(0.013)                                       | 125<br>(200)               | 50               | Polycarbonate             | U-bolt & Bracket | N/A                            |
| S1803BNF    | 1850-1990        | 3           | 140                       | 38°                           | 13<br>(33.0 x 2.5)   | 1.3<br>(0.59)        | 0.06<br>(0.006)                                       | 125<br>(200)               | 50               | Polycarbonate             | Direct           | N/A                            |
| S1800BNF    | 1850-1990        | 0           | 140                       | 70°                           | 8<br>(20.3)          | 1.2<br>(0.55)        | 0.04<br>(0.003)                                       | 125<br>(200)               | 50               | Polycarbonate             | Direct           | N/A                            |
| S1715BNF    | 1710-1880        | 5           | 170                       | 16°                           | 33<br>(83)           | 2.2<br>(0.95)        | 0.15<br>(0.014)                                       | 125<br>(200)               | 50               | Polycarbonate             | Direct           | N/A                            |
| S1713BNF    | 1710-1880        | 3           | 170                       | 38°                           | 14<br>(35.5)         | 1.4<br>(0.64)        | 0.07<br>(0.006)                                       | 125<br>(200)               | 50               | Polycarbonate             | Direct           | N/A                            |
| S1710BNF    | 1710-1880        | 0           | 170                       | 70°                           | 9<br>(22.9)          | 1.3<br>(0.59)        | 0.04<br>(0.003)                                       | 125<br>(200)               | 50               | Polycarbonate             | Direct           | N/A                            |

Common specifications: VSWR - 1.5: nominal; Connector Type - N (female); Pigtail - 12 inch (30.5 cm); Element material - printed circuit; dome diameter 1"

Americas: +1.847.839.6907  
IAS-AmericasEastSales@lairdtech.com

Europe: +44.1628.858941  
IAS-EUSales@lairdtech.com

Asia: +86.21.5855.0827.127  
IAS-AsiaSales@lairdtech.com

[www.lairdtech.com](http://www.lairdtech.com)

ANT-DS-SPOMNI 0115

Any information furnished by Laird Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird materials rests with the end user, since Laird and its agents cannot be aware of all potential uses. Laird makes no warranties as to the fitness, merchantability or suitability of any Laird materials or products for any specific or general uses. Laird shall not be liable for incidental or consequential damages of any kind. All Laird products are sold pursuant to the Laird Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2015 Laird Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Logo, and other marks are trade marks or registered trade marks of Laird Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird or any third party intellectual property rights.