

"High Frequency Ceramic Solutions"

2.45 GHz High Pass Filter

P/N 2450HP14A100

Detail Specification: 11/14/12

Page 1 of 2

General Specifications



Part Number	2450HP14A100	Impedance	50 Ω
Frequency (MHz)	2400 - 2500	Operating Temperature	-40 to +85°C
Insertion Loss	1.3 dB max.	Reel Quantity	4,000
Return Loss	14.0 dB max.	Input Power	3 W max.
Attenuation (db)	20 dB @ 1917 MHz		

Part Number Explanation

P/N Suffix	Packing Style	Bulk (Loose)	Suffix = S	eg. 2450HP14A100S
		T & R	Suffix = T	eg. 2450HP14A100T
	Evaluation Board		2450HP14A100-EB-SMA	


Mechanical Dimensions

	In	mm
L	0.063 $\pm$ 0.004	1.60 $\pm$ 0.10
W	0.031 $\pm$ 0.004	0.80 $\pm$ 0.10
T	0.022 $\pm$ 0.004	0.55 $\pm$ 0.10
a	0.008 $\pm$ 0.004	0.20 $\pm$ 0.10
b	0.008 + .004 / -.008	0.20 + 0.01 / -0.2
c	0.006 $\pm$ 0.004	0.15 $\pm$ 0.10
g	0.012 $\pm$ 0.004	0.30 $\pm$ 0.10
p	0.020 $\pm$ 0.002	0.50 $\pm$ 0.05



Terminal Configuration

No.	Function
1	IN
2	GND
3	OUT
4	NC
5	GND
6	NC




Mounting Considerations

Mount these devices with brown mark facing up.

*Line width should be designed to provide 50 Ω impedance matching characteristics.

Units: mm



LEGEND

- Solder
- Land
- Through-hole ($\phi 0.35$)

"High Frequency Ceramic Solutions"


2.45 GHz High Pass Filter

Detail Specification: 11/14/12

P/N 2450HP14A100

Page 2 of 2

Typical Electrical Performance (T=25°C)



Johanson Technology, Inc. reserves the right to make design changes without notice. Please confirm the specifications and delivery conditions when placing your order. All sales are subject to Johanson Technology, Inc. terms and conditions.



Ver 2.1

www.johansontechnology.com

4001 Calle Tecate • Camarillo, CA 93012 • TEL 805.389.1166 FAX 805.389.1821

2012 Johanson Technology, Inc. All Rights Reserved