



ESQ-110-44-T-D



ESW-115-12-G-S



ESQ-132-14-G-D

ESW, ESQ SERIES

ELEVATED SOCKET

TSW, MTSW, EW,
MTLW, TSS, ZSS, TSM,
DW, ZW, HW, TSSH, HTSS

For complete specifications
see www.samtec.com?ESW or
www.samtec.com?ESQ

Lead-Free Solderable:
Wave only

For complete scope
of recognitions see
www.samtec.com/quality



**TIGER
BUY**
CONTACT


- Other platings

Note:
Some lengths, styles and options are non-standard, non-returnable.

TYPE STRIP	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OTHER OPTION
ESW = Solder Tail	01 thru 36			-L = 10 μ" (0.25 μm) Gold contact, Matte Tin on tail	-S = Single Row	-LL = Locking Lead  Two leads per strip crimped. N/A with single row 1 or 2 positions.
ESQ = Square Tail				-G = 20 μ" (0.51 μm) Gold contact, Gold Flash on Balance	-D = Double Row	
				-T = Matte Tin (N/A w/LIF contact)	-T = Triple Row (ESQ only)	
→ (2.54) .100 X No. of Positions + (0.51) .020 ←						

Specify LEAD STYLE
from chart below.

STANDARD INSERTION FORCE	LOW INSERTION FORCE	A	B
- 12	- 37	(2.29) .090	(11.05) .435
- 13	- 38	(7.36) .290	
- 23	- 48	(4.83) .190	(13.59) .535
- 33	- 58	(2.29) .090	(16.13) .635
- 14	- 39	(12.19) .480	(11.05) .435
- 24	- 49	(9.65) .380	(13.59) .535
- 34	- 59	(7.11) .280	(16.13) .635
- 44	- 69	(4.57) .180	(18.67) .735



APPLICATIONS




Self Nesting Sockets



PC/104" J1/P1 "Stackthrough" Connectors	
Standard Insertion Force	ESQ-132-14-G-D
Low Insertion Force	ESQ-132-39-G-D
PC/104" J1 "Non-Stackthrough" Connectors	
Standard Insertion Force	ESQ-132-12-G-D
Low Insertion Force	ESQ-132-37-G-D
PC/104" J2/P2 "Stackthrough" Connectors	
Standard Insertion Force	ESQ-120-14-G-D
Low Insertion Force	ESQ-120-39-G-D

PC/104 is a trademark of the PC/104 Consortium.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

*All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.*