



QMS-PC, QFS-PC

QMS — **NO. OF PINS PER ROW** — **LEAD STYLE** — **PLATING OPTION** — **D** — **END OPTION**

Mates with: QFS-PC

-026, -052, -078
(52 total pins per bank)

Specify LEAD STYLE from chart

-L
= 10μ" (0,25μm) Gold on Signal Pins and Ground Plane
(Gold flash on Signal Pin tails, Tin on Ground Plane tails)

-PC4
= 4 Power Pins per End

Technical drawing of a connector assembly showing dimensions and lead styles. The drawing includes a side view of the connector with dimensions: (2,00) .07874, (2,29) .090, (21,35) .840, (2,54) .100, (7,52) .296, (0,635) .025, (0,23) .009, and (2,31) .091. The drawing also shows the number of banks and the total length: No. of Banks x (21,34) .840 + (13,21) .520. A table of lead styles is provided:

LEAD STYLE	A
-10	(5,38) .212
-11	(6,35) .250

QFS — **NO. OF PINS PER ROW** — **01** — **PLATING OPTION** — **D** — **END OPTION**

Mates with: QMS-PC

-026, -052, -078
(52 total pins per bank)

-L
= 10μ" (0.25μm) Gold on Signal Pins and Ground Plane
(Gold flash on Signal Pin tails, Tin on Ground Plane tails)

-PC4
= 4 Power Pins per End

Technical drawing of the QFS connector showing top and side views with dimensions. The top view shows a rectangular connector with two rows of pins. Dimensions include: No. of Banks x (21,34) .840 + (12,87) .507; (2,00) .07874; (8,13) .320; (2,10) .083; (0,635) .025; (0,23) .009; (21,34) .840; (2,54) .100; (1,78) .070; (2,54) .100. A table on the left specifies BOARD SPACE: 10mm and 11mm.

BOARD SPACE
10mm
11mm

Due to technical progress, all designs, specifications and components are subject to change without notice

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047

SAMTEC USA • Tel: +1 508 541-5511 • Fax: +1 508 541-5547
SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299
SAMTEC JAPAN • Tel: +81 3 5561 5000 • Fax: +81 3 5561 5001
SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61
SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315

SAMTEC SCANDINAVIA • Tel: +46-84477280 • Fax: +46-87420413 **SAMTEC ISRAEL** • Tel: 972-3-7526600 • Fax: 972-3-7526690 **SAMTEC INDIA** • Tel: +91-80-3272 1612 • Fax: +91-80-4152 8187

Tel: 65 6745-5955 • Fax: 65 6841-1502
Tel: 852 36004858 • Fax: 852 36004842

SAMTEC JAPAN • Tel: 045-475-1385 • Fax: 045-475-1340
SAMTEC KOREA • Tel: 82 31 717 5685 • Fax: 82 31 717 5681

SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-53854047
SAMTEC SOUTH AFRICA • Tel: 27 11 4528112 • Fax: 27 86 6714422

SAMTEC TAIWAN • Tel: 886 02 2698-31
SAMTEC ANZ • Tel: 612 95

SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502
SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842
SAMTEC JAPAN • Tel: 045-475-1385 • Fax: 045-475-1340
SAMTEC KOREA • Tel: 82-31-717-5685 • Fax: 82-31-717-5681
SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-61103765
SAMTEC SOUTH AFRICA • Tel: 27 11 4528112 • Fax: 27 86 6714432
SAMTEC INDIA • Tel: 91-60-9272-1912 • Fax: 91-60-9132-9197
SAMTEC TAIWAN • Tel: 886 02 2698-3367 • Fax: 886 02 8698-2159
SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745