



#### NOTES:

1. INSERTION LOSS: 0.75 dB MAX.
2. OPERATION TEMP: -20°C TO +70°C.
3. PRODUCT COMES WITH DUST CAPS. (NOT SHOWN)
4. MATERIALS:  
SLEEVE: SINGLE-MODE - CERAMIC (ZIRCONIA)  
MULTI-MODE - PHOSPHORUS BRONZE  
HOUSING - DELRIN, BLACK  
ADAPTER - THERMOPLASTIC  
SCREWS - STEEL, NICKEL PLATED  
ADAPTER MOUNTING CLIPS - STAINLESS STEEL
5. FOR MOUNTING SCREWS TO BE SHIPPED WITH ASSEMBLY AND INDIVIDUALING PACKAGING, ADD SUFFIX -PKG TO PART NUMBER.
6. WHEN MOUNTING ASSEMBLY, USE A SCREW TORQUE OF 10 INCH-POUNDS MAXIMUM.
7. THIS PRODUCT IS RoHS COMPLIANT.

#### RECOMMENDED PANEL CUT-OUT

PART NUMBER	LC2 ADAPTER	ADAPTER COLOR
EHLC2	SINGLE-MODE	BLUE
EHLC2M	MULTI-MODE	BEIGE

#### CUSTOMER DRAWING

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
					UNLESS OTHERWISE SPECIFIED  1. ALL DIMENSIONS IN INCHES  - TWO PLACE DECIMALS     ±0.02  - THREE PLACE DECIMALS    ±0.005	SIZE		WIDTH		MULT		LBS/M		TEMPER	
						FINISH SPEC No.						MATERIAL SPEC No.			
						FIRST USED ON				SCALE 1:1		Switchcraft®			
B	27239	1-3-14	TO	TJK		DATE DRAWN 5/12/08	BY JGK	CHKD RS 5/21/09	APVD TJK 7/16/09						
A	26348	2/27/09	RS	TJK								SHEET    1                      OF    1			
REV	ECO NUMBER	DATE	BY	APVD	NAME    E SERIES LC TO LC FIBER OPTIC ADAPTER, RoHS						PART No.                      EHLC2 SERIES				REV B
REVISIONS					DO NOT SCALE DRAWING										