


Di-Li Mikroskope



Di-Li 2055-F USB-Kamera für Mikroskope 3MP

Di-Li 2055-F USB- Microscop-Camera 3MP

USB-Kamera für Mikroskope

Spezial-Farb 1/2" USB-CMOS Kamera mit C-mount Anschluß

Zum direktem Anschluß an USB 2.0

inkl. Treiber + Software (Windows XP, Vista, Win7, Win8, Mac)

CMOS Sensor **3MP**, eingebauter IR Filter, robustes, hochwertiges Aluminiumgehäuse.

Optimiert für Stereo- u. Biologiemikroskope.

Captures crisp sharp images with 3.0 MP (2048x1536) resolution

Displays live video at 30 f/s @ 640x480 and 11 f/s @ 2048x1536 resolution

Includes advanced editing & measuring software

Supports high quality print imaging in BMP, TIFF, JPG and other formats

Compatible with Windows 2000/XP/Vista/7/8; Mac (both 32 and 64 bits)

Compatible with Twain, DirectShow, Amcap, Minisee & other third-party software

Sensor	Micron MT9T001
Color/monochrome	Color
Sensor size	1/2"
Pixel size(µm)	3.2×3.2
Effective pixels	3.0MP
Max.resolution (H×V)	2048×1536
Scan mode	Progressive
Shutter	Rolling shutter
Frame rate	10fps(2048 × 1536 Full Frame)
	25fps (1024 × 768)
	40fps (640 × 480)
Color depth	24bit
A/D	8 bit
Exposure Control	Manual/Auto
Integration Time (S)	0.001-0.5
White Balance	Manual/Auto
Dynamic range	54dB
Operating temperature	0-60℃
Cooling	—
Operating humidity	45%-85%
Storage temperature	-20-70℃
Cooling temperature	—
Operating system	Windows / Linux / Mac
Optical port	C-Mount
Data interface	USB2.0/480Mb/s