



- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 5
 - 3 - CIRCUIT DIAGRAM, CAT. LIST AND DATE CODE ARE SHOWN ON NAMEPLATE
 - 4 - SWITCH IS SKYDROL RESISTANT
 - 5 - COINCIDENCE OF OPERATING AND RELEASING POINTS:
.010 INCH OF PLUNGER TRAVEL
 - 6 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE	FULL
OPERATING FORCE -----6-12 LB		CONTACT ARRANGEMENT		DO NOT SCALE PRINT	
FULL OVERTRAVEL FORCE ----- 30LB MAX		S P D T (2)		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE ----- 4 LB MIN		LOAD	28 VDC		ONE PLACE (.0) ±.03
PRETRAVEL ----- .040 MAX			SEA LEVEL	100,000 FT.	TWO PLACE (.00) ±.01
DIFFERENTIAL TRAVEL----- .020 MAX			RES	5	THREE PLACE (.000) ±.00
OVERTRAVEL ----- .250 MIN			IND	3	ANGLES ±
		MOTOR	4	WEIGHT 11.2 OZ MAX	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1HE19-12](#)