





- 1 HOUSING MATERIAL SHALL BE LIQUID CRYSTAL POLYMER. (BLACK)
- 2 CONTACT MATERIAL SHALL BE PHOS. BRONZE. PLATING SHALL BE .000200 [0.00508] MIN. TIN/LEAD OVER .000050 [0.00127] MIN. NICKEL ALL OVER.
- 3 BASE MATERIAL SHALL BE LIQUID CRYSTAL POLYMER. (BLACK)
- 4 CONTACT MATERIAL SHALL BE PHOS. BRONZE. PLATING SHALL BE .000200 [0.00508] MIN. TIN (LEAD FREE) OVER .000050 [0.00127] MIN. NICKEL ALL OVER.

822115-4	4	6.43 [.253]	25.35 [.998]	38.20 [1.504]	2-822114-4	160
822115-3	4	7.73 [.304]	22.76 [.896]	38.20 [1.504]	2-822114-3	144
822115-4	2	6.43 [.253]	25.35 [.998]	38.20 [1.504]	822114-4	160
822115-3	2	7.73 [.304]	22.76 [.896]	38.20 [1.504]	822114-3	144
MATING COVER PART NO.	FINISH	C	B	A	PART NO.	POSN.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

± -
± -
± -
± .1mm [.004]
± -
± -
SEE TABLE

DWN
C.WHITT
8-8-91

CHK
R.MILLER
8-8-91

APVD
G.HOWEL
8-15-91

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

CUSTOMER DRAWING

TE Connectivity

NAME
MICRO-PITCH SOCKET, METRIC HOUSING SUB-ASSEMBLY FOR 28mm SQUARE, .65 PITCH PQFP

SIZE
A1

DWG CODE
00779

DRAWING NO.
822114


RESTRICTED TO
—

SCALE
10:1


SHEET
1

OF
2



REV
E1



RECOMMENDED P.C. BOARD HOLE PATTERN
SOCKET SIDE
144 POSN.



RECOMMENDED P.C. BOARD HOLE PATTERN
SOCKET SIDE
160 POSN.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.WHITT 8-9-91 CHK R.MILLER 8-9-91 APVD R.HOWEL 8-15-91		 TE Connectivity	
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME MICRO-PITCH SOCKET, METRIC HOUSING SUB-ASSEMBLY FOR 28mm SQUARE, .65 PITCH PQFP	
INCHES		0 PLC ± - 2 PLC ± - 3 PLC ± .1mm [0.004] 4 PLC ± -			
		PRODUCT SPEC - APPLICATION SPEC -			
MATERIAL -		FINISH -		SIZE A1 CAGE CODE 00779 DRAWING NO. 822114 RESTRICTED TO -	
		WEIGHT -		SCALE 1:1 SHEET 2 of 2 REV F1	
CUSTOMER DRAWING					