


DO NOT
SCALE FROM
THIS PRINT

PCT2-1XX-XX-XX-X-XX-XX

NO OF POSITIONS
-01 THRU -39 (2MM POS PER ROW)

LEAD STYLE
-03: USE T-1S13-XX-X-2

PLATING SPECIFICATION

-L: LIGHT SELECTIVE
-F: FLASH SELECTIVE
-LM: LIGHT SELECTIVE, MATTE TIN TAIL
-FM: FLASH SELECTIVE, MATTE TIN TAIL
(IF PLATING OPTION -L OR -F IS SELECTED, USE T-1S8-01-T. IF
PLATING OPTION -LM OR -FM IS SELECTED, USE T-1S8-01-T.)

OPTION 1



-RA: RIGHT ANGLE
(SEE FIG. 2, SHEET 2)

POWER POSITIONS

-04, -03, -02, -01

ROW SPECIFICATION

-D: DOUBLE ROW



NOTES:

1. MAXIMUM ALLOWABLE BOW: .005 [0.13] INCH/INCH AFTER ASSEMBLY.
2. MAXIMUM PIN ROTATION IN BODY: 2<MOD-DEG>.
3. MINIMUM PUSHOUT FORCE: 1 lb.
4. (C) REPRESENTS A CRITICAL DIMENSION.
5. ENDWALL THICKNESS: .022 ON SIGNAL END / .064 ON POWER END.
6. MEASURE AT BEND RADIUS, NOT END OF PIN.
7. MAXIMUM ALLOWABLE CUT FLASH: .015 [0.38].
8. TAILS SHEARED ON POWER PINS (.045 [1.14] SQ.) TO DIMENSION SHOWN (.005 [0.13] MAX BURR)
9. 120 MAX TAIL DUE TO MULTI-CUT ISSUE.
10. LAYER PACKAGE POSITIONS 1-4, TUBE POSITIONS 5-39.

DELETED

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES
.XX: ±.01 2°
.XXX: ±.005
.XXXX: ±.0020

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING
INSULATOR: VECTRA E130i
COLOR: BLACK

TERMINAL(S): 510 PHOS BRONZE

F:\DWG\MISC\MKTG\PCT2-1XX-XX-XX-X-XX-XX-MKT.SLDDRW

SHEET SCALE: 1.5:1

SAMTEC

520 PARK EAST BLVD, NEW ALBANY, IN 47150
* PHONE: 812.944.6733 FAX: 812.948.5047
e-Mail: INFO@SAMTEC.COM CODE: 55322

DESCRIPTION:




2MM TERMINAL/POWER COMBO -RA ASM

DWG. NO.


PCT2-1XX-XX-XX-X-XX-XX

BY: T.WERNE 11/01/00

SHEET 1 OF 2




USE PT-1-24-01-45
& TP-07




USE PT-1-24-02-17
& TP-09





FIG 2
-RA OPTION



IN-PROCESS 2



IN-PROCESS 3



PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1.5:1

S A M T E C

520 PARK EAST BLVD, NEW ALBANY, IN 47150
* PHONE: 812.944.6733 FAX: 812.948.5047
e-Mail: INFO@SAMTEC.COM CODE: 55322

DESCRIPTION:
2MM TERMINAL/POWER COMBO -RA ASM

DWG. NO. PCT2-1XX-XX-XX-X-XX-XX

BY: T.WERNE	11/01/00	SHEET 2 OF 2
-------------	----------	--------------