

Sta-Kon®

Splice Connectors



Vinyl Insulated Splices – Butt Type – Expanded Insulation

Cat. No.	Pkg. Qty.	Wire Range	Max. Ins.	Wt./Lbs. Per 1000	Dimensions	
					A	B
2RA18X	100	22-18	.155	3	1.13	.25
RAA217-170	1000	22-18	.170	3	1.13	.25
RAA217	1000	22-18	.155	3	1.13	.23
2RB14X	100	16-14		3	1.13	.26
RBB217-200	1000	16-14	.200	3	1.13	.26
RBB217	1000	16-14		3	1.13	.23
2RC10X	50	12-10	.210	7	1.31	.31
RCC217-250	500	12-10	.250	7	1.31	.31
RCC217	1000	12-10	.210	7	1.31	.29

U.L. Listed E9809

Installing tools: WT145C, WT2000, WT112M, ERG-2001, ERG-2003

Bulk No's: RAA22X – RBB22X – RCC22X



These butt splices are self-insulated with heat shrinkable polyolefin and internally coated sealant. Upon completed installation, a fully sealed connection is achieved to protect the joint against the degrading effects of galvanic action, corrosion, and environmental exposure.

Heat Shrinkable Splices – Butt Type – Expanded Insulation

Cat. No.	Pkg. Qty.	Wire Range	Max. Ins.	Wt./Lbs. Per 1000	Dimensions	
					A	B
2RAS18X	50	22-18	.170	3	1.50	.25
RAAS22X	500	22-18	.170	3	1.50	.25
2RBS14X	50	16-14	.200	3	1.50	.26
RBBS22X	500	16-14	.200	3	1.50	.26
2RCS10X	25	12-10	.250	7	1.60	.31
RCCS22X	250	12-10	.250	7	1.60	.31

Installing tool: WT1255



A, B & C bulk numbers can be put on Mylar Tape for reel fed applications (i.e. 12050 tool and application dies). See pages K61- K62. Please put the suffix M for Mylar Tape RA2573M. (Bulk number 1000 and 500 packages.)


Non-Insulated Splices – Butt Type

Cat. No.	Pkg. Qty.	Wire Range	Wt./Lbs. Per 1000	Dimensions	
				A	B
2A-18	100	22-18	2½	.62	.12
AA2	1000	22-18	2½	.62	.12
2B-14	100	16-14	2½	.62	.16
BB2	1000	16-14	2½	.62	.16
2C-10	50	12-10	7	.72	.22
CC2	500	12-10	7	.72	.22
2D-8	25	9-8-7	18	1.03	.28
DD102	200	9-8-7	18	1.03	.28
2E-6	20	6-5	25	1.12	.37
EE2	200	6-5	25	1.12	.37
2F-4	15	4-3	30	1.25	.44
FF2	200	4-3	30	1.25	.44
2G21	5	2-1	40	1.72	.55
GG2	25	2-1	40	1.72	.55

U.L. Listed E9809

Installing tools – A, B, C: WT111M, WT110M, WT2000, ERG-2002, WT112M

Installing tools – D, E, F, G: WT115A, TBM6/TBM6S



K

Sta-Kon®

Thomas & Betts