

PRECISION BOARD STACKING STANDOFF

SO SERIES

SO

Use With:

QXH, QXE, QXS,
QXSS, QRX8, ERX5,
ERX6, ERX8, LSHM,
LSS, LSEM, SX4, SX5, XLH

SPECIFICATIONS


Material:

Aluminum

Locking Compound:

Nylon

INDUSTRY STANDARD SOLUTIONS



Requires Standoff
SO-1524-03-01-01-L or
JSOM-1524-02 for 15.24 mm
or SO-2200-03-01-01-L
for 22 mm board spacing.
Connectors designed to not
fully seat when mated.

For more information on the JSOM,
visit samtec.com?JSOM

INDUSTRY STANDARD	INTERCONNECTS			
	TERMINAL	SOCKET	BANKS	STACK HEIGHT
SUMIT™	ASP-129637-01	ASP-129646-01	1	15.24 mm
PCI/104-Express™	ASP-129637-03	ASP-129646-03	3	15.24 mm
PCI/104-Express™	ASP-129637-13	ASP-129646-22	1	15.24 mm
PCI/104-Express™	ASP-142781-01	ASP-129646-01	1	22 mm
PCI/104-Express™	ASP-142781-02	ASP-129646-02	2	22 mm
PCI/104-Express™	ASP-142781-03	ASP-129646-03	3	22 mm

ALSO AVAILABLE

Contact Samtec


Other heights
Stainless Steel
Locking compound removed
Other materials and threading
No Hardware

Note:

Some sizes, styles and
options are non-standard,
non-returnable.

SO	BOARD STACKER	LEAD STYLE	THREAD STYLE	01	L
	Specify BOARD STACKER from chart	-01 = Female Thread/Press-In (-0515 thru -0865 only)	-01 = #4-40 Thread		-L = -02 & -03 Lead Style thread locking compound (Leave blank for -01 Lead Style)
		-02 = Male/Male Thread (-0515 and -1115 thru -2515 only)	-02 = M3 x 0.5 Thread°		
		-03 = Male/Female Thread (-0815 thru -2515 only)			
		-05 = Female/Female Thread (-0515 thru -2515 only)			

BOARD STACKER	A	BOARD STACK HEIGHT
-0515	(5.15) .203	5 mm
-0715	(7.15) .282	7 mm
-0815	(8.15) .321	8 mm
-0865	(8.65) .341	8.5 mm
-1115	(11.15) .439	11 mm
-1215	(12.15) .478	12 mm
-1524	(15.24) .600	15.09 mm
-1615	(16.15) .636	16 mm
-1890	(18.90) .744	18.75 mm
-1915	(19.15) .754	19 mm
-2515	(25.15) .990	25 mm



Components are to be packaged in separate bags unassembled.