

C1608X8R1H102K080AA

TDK Item Description : C1608X8R1H102KT****




Application & Main Feature


Commercial Grade (High Temperature Application)

Series

C1608 [EIA CC0603]



DC Bias Characteristic



Dimensions

L 1.60mm +/-0.1mm
W 0.80mm +/-0.1mm
T 0.80mm +/-0.1mm
B 0.20mm Min.
G 0.30mm Min.

Temperature Characteristic

X8R (-55 to 150 degC +/-15%)

Rated Voltage

1H (50Vdc)

Capacitance

1nF

Capacitance Tolerance

K (+/-10%)

Dissipation Factor

3% Max.


Insulation Resistance

10Gohm Min.


AEC-Q200

Not Applicable


|Z|, ESR vs. Freq. Characteristics



Temperature Characteristic



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristic

