



Micro Commercial Components



Micro Commercial Components  
20736 Marilla Street Chatsworth  
CA 91311  
Phone: (818) 701-4933  
Fax: (818) 701-4939

**2EZ5.1D5  
THRU  
2EZ75D5**

## Features

- Glass Passivation Junction
- Lead Free Finish/RoHS Compliant (Note C) ("P" Suffix designates Compliant. See ordering information)
- Excellent Clamping Capability
- Halogen free available upon request by adding suffix "-HF"

## Mechanical Data

- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- TERMINALS : Solder plated, solderable per MIL-STD-750, method 2026
- POLARITY : Color band denotes positive end (cathode)

### Maximum Ratings @ 25°C Unless Otherwise Specified


|                                                                                                           |                                       |                            |                        |
|-----------------------------------------------------------------------------------------------------------|---------------------------------------|----------------------------|------------------------|
| Steady Power Dissipation (Note A)<br>Derate above 75°C                                                    | <b>P<sub>D</sub></b>                  | <b>2<br/>36</b>            | <b>Watts<br/>mW/°C</b> |
| Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method) (Note B) | <b>I<sub>FSM</sub></b>                | <b>15</b>                  | <b>Amps</b>            |
| Operating And Storage Temperature Range                                                                   | <b>T<sub>J</sub>, T<sub>STG</sub></b> | <b>-55°C to<br/>+150°C</b> |                        |

#### NOTES:

- A. Mounted on 5.0mm<sup>2</sup> (.013mm thick) land areas.
- B. Measured on 8.3ms, single half sine-wave or equivalent square wave, duty cycle = 4 pulses per minute maximum.
- C. High Temperature Solder Exemption Applied, see EU Directive Annex 7.

**2 W Glass Passivated  
Junction Silicon  
Zener Diode  
5.1-75 Volts**

DO-41



| DIMENSIONS |        |      |       |      |      |
|------------|--------|------|-------|------|------|
| DIM        | INCHES |      | MM    |      | NOTE |
|            | MIN    | MAX  | MIN   | MAX  |      |
| A          | .166   | .205 | 4.10  | 5.20 |      |
| B          | .080   | .107 | 2.00  | 2.70 |      |
| C          | .028   | .034 | .70   | .90  |      |
| D          | 1.000  | ---  | 25.40 | ---  |      |

**www.mccsemi.com**

## 2EZ5.1D5 THRU 2EZ75D5

Micro Commercial Components

ELECTRICAL CHARACTERISTICS ( $T_A=25^{\circ}\text{C}$  unless otherwise noted)  $V_F=1.2\text{ V max}$ ,  $I_F=200\text{ mA}$  for all types

| Type No.<br>(Note 1.) | Nominal Zener<br>Voltage $V_Z@I_{ZT}$<br>volts<br>(Note 2.) | Test<br>current<br>$I_{ZT}$<br>mA | Maximum Zener Impedance (Note 3) |                   |          | Leakage Current   |       | Maximum Zener<br>Current<br>$I_{ZM}$<br>mA |
|-----------------------|-------------------------------------------------------------|-----------------------------------|----------------------------------|-------------------|----------|-------------------|-------|--------------------------------------------|
|                       |                                                             |                                   | $Z_{ZT} @ I_{ZT}$                | $Z_{ZK} @ I_{ZK}$ | $I_{ZK}$ | $I_R$             | $V_R$ |                                            |
|                       |                                                             |                                   | Ohms                             | Ohms              | mA       | $\mu\text{A Max}$ | Volts |                                            |
| 2EZ5.1D5              | 5.1                                                         | 98                                | 3.5                              | 600               | 1        | 5.0               | 1.0   | 356                                        |
| 2EZ5.6D5              | 5.6                                                         | 89.5                              | 2.5                              | 500               | 1        | 5.0               | 2.0   | 324                                        |
| 2EZ6.2D5              | 6.2                                                         | 80.5                              | 1.5                              | 700               | 1        | 5.0               | 3.0   | 292                                        |
| 2EZ6.8D5              | 6.8                                                         | 73.5                              | 2.0                              | 700               | 1        | 5.0               | 4.0   | 266                                        |
| 2EZ7.5D5              | 7.5                                                         | 66.5                              | 2.0                              | 700               | 0.5      | 5.0               | 5.0   | 242                                        |
| 2EZ8.2D5              | 8.2                                                         | 61                                | 2.3                              | 700               | 0.5      | 5.0               | 6.0   | 220                                        |
| 2EZ9.1D5              | 9.1                                                         | 55                                | 2.5                              | 700               | 0.5      | 3.0               | 7.0   | 200                                        |
| 2EZ10D5               | 10                                                          | 50                                | 3.5                              | 700               | 0.25     | 3.0               | 7.6   | 182                                        |
| 2EZ11D5               | 11                                                          | 45.5                              | 4.0                              | 700               | 0.25     | 1.0               | 8.4   | 166                                        |
| 2EZ12D5               | 12                                                          | 41.5                              | 4.5                              | 700               | 0.25     | 1.0               | 9.1   | 152                                        |
| 2EZ13D5               | 13                                                          | 38.5                              | 5.0                              | 700               | 0.25     | 0.5               | 9.9   | 138                                        |
| 2EZ14D5               | 14                                                          | 35.7                              | 5.5                              | 700               | 0.25     | 0.5               | 10.6  | 130                                        |
| 2EZ15D5               | 15                                                          | 33.4                              | 7.0                              | 700               | 0.25     | 0.5               | 11.4  | 122                                        |
| 2EZ16D5               | 16                                                          | 31.2                              | 8.0                              | 700               | 0.25     | 0.5               | 12.2  | 114                                        |
| 2EZ17D5               | 17                                                          | 29.4                              | 9.0                              | 750               | 0.25     | 0.5               | 13.0  | 107                                        |
| 2EZ18D5               | 18                                                          | 27.8                              | 10                               | 750               | 0.25     | 0.5               | 13.7  | 100                                        |
| 2EZ19D5               | 19                                                          | 26.3                              | 11                               | 750               | 0.25     | 0.5               | 14.4  | 95                                         |
| 2EZ20D5               | 20                                                          | 25                                | 11                               | 750               | 0.25     | 0.5               | 15.2  | 90                                         |
| 2EZ22D5               | 22                                                          | 22.8                              | 12                               | 750               | 0.25     | 0.5               | 16.7  | 82                                         |
| 2EZ24D5               | 24                                                          | 20.8                              | 13                               | 750               | 0.25     | 0.5               | 18.2  | 76                                         |
| 2EZ27D5               | 27                                                          | 18.5                              | 18                               | 750               | 0.25     | 0.5               | 20.6  | 68                                         |
| 2EZ30D5               | 30                                                          | 16.6                              | 20                               | 1000              | 0.25     | 0.5               | 22.5  | 60                                         |
| 2EZ33D5               | 33                                                          | 15.1                              | 23                               | 1000              | 0.25     | 0.5               | 25.1  | 55                                         |
| 2EZ36D5               | 36                                                          | 13.9                              | 25                               | 1000              | 0.25     | 0.5               | 27.4  | 50                                         |
| 2EZ39D5               | 39                                                          | 12.8                              | 30                               | 1000              | 0.25     | 0.5               | 29.7  | 47                                         |
| 2EZ43D5               | 43                                                          | 11.6                              | 35                               | 1500              | 0.25     | 0.5               | 32.7  | 43                                         |
| 2EZ47D5               | 47                                                          | 10.6                              | 40                               | 1500              | 0.25     | 0.5               | 35.8  | 39                                         |
| 2EZ51D5               | 51                                                          | 9.8                               | 48                               | 1500              | 0.25     | 0.5               | 38.8  | 36                                         |
| 2EZ56D5               | 56                                                          | 9.0                               | 55                               | 2000              | 0.25     | 0.5               | 42.6  | 32                                         |
| 2EZ62D5               | 62                                                          | 8.1                               | 60                               | 2000              | 0.25     | 0.5               | 47.1  | 29                                         |
| 2EZ68D5               | 68                                                          | 7.4                               | 75                               | 2000              | 0.25     | 0.5               | 51.7  | 27                                         |
| 2EZ75D5               | 75                                                          | 6.7                               | 90                               | 2000              | 0.25     | 0.5               | 56.0  | 24                                         |

### Notes:

1. TOLERANCES - Suffix indicates 5% tolerance any other tolerance will be considered as a special device.
2. ZENER VOLTAGE ( $V_Z$ ) MEASUREMENT - guarantees the zener voltage when measured at 40 ms from the diode body, and an ambient temperature of 25
3. ZENER IMPEDANCE ( $Z_Z$ ) DERIVATION - The zener impedance is derived from the 60 cycle ac voltage, which results when an ac current having an rms value equal to 10% of the dc zener current ( $I_{ZT}$  or  $I_{ZK}$ ) is superimposed on  $I_{ZT}$  or  $I_{ZK}$

## RATING AND CHARACTERISTICS CURVES

2EZ5.1D5 THRU 2EZ75D5

**M.C.C.**

Micro Commercial Components




Fig. 1-TYPICAL THERMAL RESPONSE




Fig. 2-MAXIMUM SURGE POWER




Fig. 3-TYPICAL REVERSE LEAKAGE




Fig. 4-UNITS 3.9 TO 12 VOLTS




Fig. 5-UNITS 10 TO 200 VOLTS

# RATING AND CHARACTERISTICS CURVES

## 2EZ5.1D5 THRU 2EZ75D5




Fig. 6-VZ = 3.9 THRU 10 VOLTS




Fig. 7-VZ = 12 THRU 82 VOLTS




Fig. 8-VZ = 100 THRU 200 VOLTS




Fig. 9-TYPICAL THERMAL RESISTANCE




Fig. 10- POWER TEMPERATURE DERATING CURVE



Micro Commercial Components

## Ordering Information :

| Device         | Packing                      |
|----------------|------------------------------|
| Part Number-TP | Tape&Reel: 5Kpcs/Reel        |
| Part Number-AP | Ammo Packing: 5Kpcs/Ammo Box |
| Part Number-BP | Bulk: 50Kpcs/Carton          |

Note : Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp .** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp .** and all the companies whose products are represented on our website, harmless against all damages.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.