

W7083SYD/H SUPER BRIGHT YELLOW


Features

- OUTSTANDING MATERIAL EFFICIENCY.
- RELIABLE AND RUGGED.
- I.C. COMPATIBLE.

Description

This devices are made with TS InGaAIP.

Package Dimensions



Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25(0.01")$ unless otherwise noted.
3. Lead spacing is measured where the lead emerge package.
4. Specifications are subject to change without notice.

Selection Guide

| | Dice | Lens Type | I _v (mcd) @ 20 mA | | Viewing Angle |
|------------|------------------------------|-----------------|---------------------------------|------|------------------|
| | | | Min. | Typ. | |
| W7083SYD/H | SUPER BRIGHT YELLOW(InGaAlP) | YELLOW DIFFUSED | 180 | 420 | 60° |

Note:

1. θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

Electrical / Optical Characteristics at T_A=25°C


| Symbol | Parameter | Device | Typ. | Max. | Units | Test Conditions |
|----------------|--------------------------|---------------------|------|------|-------|---------------------------|
| λpeak | Peak Wavelength | Super Bright Yellow | 590 | | nm | I _f =20mA |
| λ D | Dominate Wavelength | Super Bright Yellow | 589 | | nm | I _f =20mA |
| Δλ1/2 | Spectral Line Half-width | Super Bright Yellow | 20 | | nm | I _f =20mA |
| C | Capacitance | Super Bright Yellow | 45 | | pF | V _F =0V;f=1MHz |
| V _F | Forward Voltage | Super Bright Yellow | 2.3 | 2.8 | V | I _f =20mA |
| I _R | Reverse Current | Super Bright Yellow | | 10 | uA | V _R = 5V |

Absolute Maximum Ratings at T_A=25°C

| Parameter | Super Bright Yellow | Units |
|-------------------------------|---------------------|-------|
| Power dissipation | 120 | mW |
| DC Forward Current | 30 | mA |
| Peak Forward Current [1] | 140 | mA |
| Reverse Voltage | 5 | V |
| Operating/Storage Temperature | -40°C To +85°C | |
| Lead Solder Temperature [2] | 260°C For 5 Seconds | |

Notes:

1. 1/10 Duty Cycle, 0.1ms Pulse Width.
2. 2mm below package base.



Super Bright Yellow

W7083SYD/H

