


ESY, Aluminum Electrolytic, 105C LowZ, 470 uF, 20%, 25 V, -40/+105C, Lead Spacing = 3.5mm



Note: '()' correspond to the letters used in the product bulletin

Dimensions

| | |
|-------------|----------------|
| D | 8mm +/-0.5mm |
| L | 20mm +2mm |
| S | 3.5mm +/-0.5mm |
| LL Negative | 15mm MIN |
| LL Positive | 20mm MIN |
| F | 0.6mm NOM |

Packaging Specifications

| | |
|---------------------|-----------|
| Packaging: | Bulk, Bag |
| Packaging Quantity: | 4000 |

General Information

| | |
|--------------|---|
| Supplier: | KEMET |
| Series: | ESY |
| Dielectric: | Aluminum Electrolytic |
| Description: | LowZ Single Ended Aluminum Electrolytic |
| Features: | Low Z |
| RoHS: | Yes |
| Lead: | Wire Leads |

Specifications

| | |
|--------------------------|--------------------------|
| Capacitance: | 470 uF |
| Capacitance Tolerance: | 20% |
| Voltage DC: | 25 VDC, 32 VDC (Surge) |
| Temperature Range: | -40/+105C |
| Rated Temperature: | 105C |
| Life: | 3000 Hrs |
| Dissipation Factor: | 14.000000000000002% |
| Resistance: | 0.041 Ohms (100kHz) |
| Current: | 1250 mAmps (100kHz 105C) |
| Leakage Current: | 117.5 uA (2min 20C) |
| Impedance Ratio at -25C: | 2 |
| Impedance Ratio at -40C: | 3 |