

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONIC CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES (TE). IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TE PERSONNEL WITHOUT AUTHORIZATION FROM TE.

DWG. NO. 964 779
VERWENDET FÜR
THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
DIS






LOC
AI
DIST
—

PASSEND ZU —

3306-7 (3/11)

USED ON 966615


SUITABLE CONTACTS: IDC-AWG30-26 PN 215 192
PASSENDE KONTAKTE: IDC-AWG26-22 PN 215 141
CRIMP-AWG32-28 PN 167 041
CRIMP-AWG26-20 PN 166 500



OBSOLETE

964 779-2		HOUSING	PBT GF	BLACK
964 779 1		HOUSING	PBT GF	BLACK
PART NUMBER		DESCRIPTION	MATERIAL	COLOR
DWN M.Bleicher		28.11.94	MATERIAL	HEAT TREAT
CHK Krämer		28.11.94	PBTP GF	-
APVD Krämer		28.11.94	 TE Connectivity	
NAME RV100-3 2x8 POS. MT HOUSING RV100-3 2x8 POL. MT BUCHSENGEH				
SCALE 5:1	SIZE A3	DRAWING NO 964779		SHEET 1 OF 1
				REV C1

	C	REVOSED PER ECR-11-014637	18JUL2011	KS	MQ.W
P	LTR	REVISION RECORD	DATE	DWN	APVD

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.2 3 PLC ± — 4 PLC ± —
ANGLES ± 2°	
SURFACE TEXTURE 	