




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		U1	REVISED PER ECO-14-011424	23SEP14	MGM	CO



E F F E C T	71.12	[2.800]	28	5-641122-8
	68.58	[2.700]	27	5-641122-7
	66.04	[2.600]	26	5-641122-6
	63.50	[2.500]	25	5-641122-5
	60.96	[2.400]	24	5-641122-4
	58.42	[2.300]	23	5-641122-3
	55.88	[2.200]	22	5-641122-2
	53.34	[2.100]	21	5-641122-1
	50.80	[2.000]	20	5-641122-0
	48.26	[1.900]	19	4-641122-9
	45.72	[1.800]	18	4-641122-8
	43.18	[1.700]	17	4-641122-7
	40.64	[1.600]	16	4-641122-6
	38.10	[1.500]	15	4-641122-5
	35.56	[1.400]	14	4-641122-4
	33.02	[1.300]	13	4-641122-3
	30.48	[1.200]	12	4-641122-2
	27.94	[1.100]	11	4-641122-1
	25.40	[1.000]	10	4-641122-0
	22.86	[.900]	9	3-641122-9
	20.32	[.800]	8	3-641122-8
	17.78	[.700]	7	3-641122-7
	15.24	[.600]	6	3-641122-6
	12.70	[.500]	5	3-641122-5
10.16	[.400]	4	3-641122-4	
7.62	[.300]	3	3-641122-3	
5.08	[.200]	2	3-641122-2	
DIM (L)			NO.OF POSN	ASSEMBLY

CONTAINS LEAD	71.12	[2.800]	28	2-641122-8	SUPERSEDED BY 5-641122-8	16
	68.58	[2.700]	27	2-641122-7	SUPERSEDED BY 5-641122-7	16
	66.04	[2.600]	26	2-641122-6	SUPERSEDED BY 5-641122-6	16
	63.50	[2.500]	25	2-641122-5	SUPERSEDED BY 5-641122-5	16
	60.96	[2.400]	24	2-641122-4	SUPERSEDED BY 5-641122-4	16
	58.42	[2.300]	23	2-641122-3	SUPERSEDED BY 5-641122-3	16
	55.88	[2.200]	22	2-641122-2	SUPERSEDED BY 5-641122-2	16
	53.34	[2.100]	21	2-641122-1	SUPERSEDED BY 5-641122-1	16
	50.80	[2.000]	20	2-641122-0	SUPERSEDED BY 5-641122-0	16
	48.26	[1.900]	19	1-641122-9	SUPERSEDED BY 4-641122-9	16
	45.72	[1.800]	18	1-641122-8	SUPERSEDED BY 4-641122-8	16
	43.18	[1.700]	17	1-641122-7	SUPERSEDED BY 4-641122-7	16
	40.64	[1.600]	16	1-641122-6	SUPERSEDED BY 4-641122-6	16
	38.10	[1.500]	15	1-641122-5	SUPERSEDED BY 4-641122-5	16
	35.56	[1.400]	14	1-641122-4	SUPERSEDED BY 4-641122-4	16
	33.02	[1.300]	13	1-641122-3	SUPERSEDED BY 4-641122-3	16
	30.48	[1.200]	12	1-641122-2	SUPERSEDED BY 4-641122-2	16
	27.94	[1.100]	11	1-641122-1	SUPERSEDED BY 4-641122-1	16
	25.40	[1.000]	10	1-641122-0	SUPERSEDED BY 4-641122-0	16
	22.86	[.900]	9	-641122-9	SUPERSEDED BY 3-641122-9	16
20.32	[.800]	8	-641122-8	SUPERSEDED BY 3-641122-8	16	
17.78	[.700]	7	-641122-7	SUPERSEDED BY 3-641122-7	16	
15.24	[.600]	6	-641122-6	SUPERSEDED BY 3-641122-6	16	
12.70	[.500]	5	-641122-5	SUPERSEDED BY 3-641122-5	16	
10.16	[.400]	4	641122-4		16	
7.62	[.300]	3	-641122-3	SUPERSEDED BY 3-641122-3	16	
5.08	[.200]	2	-641122-2	SUPERSEDED BY 3-641122-2	16	
	DIM (L)	NO.OF POSN	ASSEMBLY			

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 261-2 JAN-2005 S. HOOVER OK: D. BOSSI 26-JAN-2005 26-JAN-2005		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MTA-.100 HEADER ASSEMBLY, PLAIN, .025 SQUARE STRAIGHT POST .00015 GOLD PLATED	
 0. PLC ± 1. PLC ± 2. PLC ± 0.13 [.025] 3. PLC ± 4. PLC ± ANGLES ± FINISH		APVD D. BOSSI 26-JAN-2005 PRODUCT SPEC APPLICATION SPEC		SIZE CAGE CODE DRAWING NO A1 00779 C=641122	
MATERIAL 		WEIGHT 		RESTRICTED TO CUSTOMER DRAWING SCALE 8:1 SHEET 1 of 1 REV U	