

FLAT PANEL MONITORS

39LV081A71UN

8.4" LCD MODULES

DISPLAY

Type:	AM Colour TFT
No. Colours:	256k
Max. Resolution:	800 x 600 pixels
Active Display Area	170.4 x 127.8 mm
Backlight:	Dual Edge CFL x 2
Backlight Life:	50,000 hours typical
Brightness:	350 cd/m ² typical
Contrast Ratio:	500:1 typical
Viewing Angles:	120° H, 100°V

SIGNAL INPUTS

Video:	Analog RGB 0.7V p-p OR TTL RGB >2.75Vp-p (via special TTL accessory cable)
Input Connector:	15-pin HD Female
Sync. Type/Level:	Separate H&V (+/-ve) TTL or Composite (-ve) TTL or Sync-on-Green (-ve) 0.3V
Multiscan Support:	800 x 600 SVGA 640 x 480 VGA + pre-programmed timings in 15-30kHz range
Horizontal Scan:	15 – 60kHz
Vertical Scan:	40 – 100Hz
Clock Rate:	80MHz max.
Controls: (On Screen Display buttons at rear)	Brightness, Contrast, H/V Position & Size, Frequency, Frequency Fine

POWER INPUTS

AC Model:	110-220V
Power Consumption:	25W Max.

PHYSICAL / ENVIRONMENTAL

Front Panel:	Black Painted Aluminium
Dimensions (approx):	246.6 x 191.4 x 68.5 mm
Weight (approx):	2.5kg. approx.
Operating Temp:	0 to 50° C
Storage Temp:	-20 to 60° C

PART NUMBERS

Standard Model	39LV081A71UN
----------------	--------------

CRT Monitor Replacements



- **For 10" Colour CRT Monitor Replacement**
- **Front Plate to suit 10" CRT Fixing Lugs**
- **Original CRT Chassis Stays in Place**
- **Analogue + TTL Video inputs**
- **Non-standard Legacy signals easily programmed**
- **Non-Glare Toughened Glass for TFT protection**
- **Optional Touchscreen Integration**

The **39LV081A71UN** Industrial LCD monitor has been designed as replacement for 10" CRT monitors now that supplies of 10" CRTs are difficult to obtain.

KME has designed a rugged LCD monitor module, of minimum width, to match the dimensions of many 10" CRT monitor chassis. When the CRT is removed from the existing chassis metalwork the LCD monitor (mounted on a metal panel with fixing holes to match the CRT Lugs) can be fitted in place.


A wide range of signal timings from 15kHz up to VGA standard, including CGA & EGA legacy signals can be accepted by the LCD monitor. Set-up controls for fine-tuning of the display are located at the rear of the monitor. Once set, no further adjustments should be required, and the last setting is stored in memory.

Accessory cables for 9D-15D and BNC-15D are available, as are special cables for non-standard interfaces.

Note: The Active Display Area on a 10" Colour CRT is typically 175 x 130 mm. On the 8.4" TFT it is 170.4 x 127.8 mm maximum.

Due to a policy of continuous product development KME reserves the right to change specifications and descriptions without prior notification. All trade marks acknowledged. 39lv081A71UN 05/2008





All dimensions in Millimetres
(Not to scale)