






P/N H1105B

FILM PET DF: thickness : 0.230 mm
FILM PET SF: thickness : 0.145 mm



SECTION A-A
SCALE 1.000



NOTE: BLACKS CABLES UNLESS OTHERWISE SPECIFIED

TOLERANCES UNLESS OTHERWISE SPECIFIED

Mark with
H1105A
REV. proj_revision
in area indicated
by X.....

rev ecn no dr date

A N06-0242 MOR 14/09/06

B N07-0015 MOR 01/11/06

- - - - -

LINEAR 0.X ±0.5 - - - - -

0.XX ±0.3 - - - - -

0.XXX ±0.1 - - - - -

ANGULAR 0° ±2° - - - - -

Material

Mat code

Heat treat

Plating/Finish

Spec ref

✓

tolerance

projection

MM

size

A4

Scale

0.250

ECN

Model Name

Model Revision

REL Level



H1105B

title

dwg no

10072967

Rev.

B

Pro/E file

catalog no

CUSTOMER


sheet 1 of 2



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

FCI CONFIDENTIAL

CONNECT UP CABLE ITEM NO 16
CONNECT UP CABLE ITEM NO 17
CONNECTORS J2A AND J4A
NOTE ORIENTATION OF WIRES



Material		Spec ref	tolerance	projection	MM
Mat code	Heat/treat	✓			
Plating/Finish					
Dr	Robbi Mo	14/09/06			
Eng	Robbi Mo	14/09/06	Product family	BUSBAR	size A4 Scale 0.250
Chr	PH DENG	14/09/06	Model Name		ECN
Appr	PH DENG	14/09/06	Model Revision		REL Level
	title	H1105B	dwg no	10072967	Rev. B
Pro/E file	catalog no		CUSTOMER	sheet 2 of 2	

REV F: 2006-04-17

1

2

3

4

PDM: Rev:B

STATUS: Released

Printed: Nov 04, 2010



52613FCI

820969FCI-001

NOTE:

1. THE REVISION OF 52613FCI AND 820969FCI-001 IS B.
2. THE PRODUCT SAP/NCM CODE:081684A.206.

A

B

C

D