




CATALOG LISTING	
12HM12-2	
ISSUE	M
REVISIONS	A 0094220
DATE	24 MAR 99
RELEASE NO.	PR-22432
PAGE	1 OF 1
CHECK	
DDM/CAD	K D R 13 NOV 96
DRAWN	



3X NO. 20 WIRE LEAD PER MIL-W-22759/11
MARKED WITH CIRCUIT IDENT AND WIRE GAGE
(C-20, NO-20, NC-20) PER MIL-W-5088



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF ϕ .087 MAX ON .375 ±.002 CENTERS
- 2 FOR USE IN TEMPERATURE RANGE -85°F TO +250°F (DOWN TO -300°F IF WIRE LEADS ARE NOT FLEXED)
- 3 HERMETICALLY SEALED (METAL-TO-METAL, GLASS-TO-METAL)
- 4 ALL EXPOSED PARTS ARE OF CORROSION RESISTANT MATERIALS
- 5 WEIGHT OF SWITCH ONLY IS 0.22 OZ MAX. WEIGHT OF CONDUCTOR GROUP ONLY IS 0.09 OZ MAX PER FOOT
- 6 DO NOT APPLY MORE THAN 1 1/2 INCH LBS OF TORQUE WHEN TIGHTENING MOUNTING SCREWS

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CHARACTERISTICS	ELECTRICAL DATA			SCALE 2 : 1	DO NOT SCALE PRINT
OPERATING FORCE	CONTACT ARRANGEMENT S P D T			UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE	LINE VOLTAGE	INDUCTIVE LOAD	RESISTIVE LOAD	ONE PLACE (.0)	± .030
DIFFERENTIAL TRAVEL	28 VDC	1 AMP	3 AMP	TWO PLACE (.00)	± .015
OVERTRAVEL	115 VAC (400 CYCLE)	1 AMP	3 AMP	THREE PLACE (.000)	± .005
				ANGLES	±
				WEIGHT	/5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[12HM12-2](#)