

PART NO.	ENG. NO.	DIM. "A" 
18-09-2803	2282-(P90 I)	
18-09-2804	2282-(P90 I) L	.161±.004/(4.09±0.10)
18-09-2807	2282-(P90 I) L I	.215±.005/(5.46±0.13)
	-	
	-	
	-	

LEGEND




2282-(****)**

P=PREPLATE
BLANK=POSTPLATE




CARRIER CUTOFF WIDTH
(ONLY APPLIES TO FORM "L")
BLANK=.161±.004
L=.215±.005

FINISH CODE

FORM
BLANK=CHAIN
L=LOOSE




SECTION A-A SECTION B-B



SECTION D-D


- NOTES:
1. TERMINAL WILL ACCEPT 14 - 18 AWG WIRE.
 2. TERMINAL FOR CHRYSLER CORP. USE ONLY.
 3. WHERE DENOTED, THIS DIMENSION TO BE .140-.145/(3.56-3.68) WHEN LOCK TABS ARE COMPRESSED TO .136-.142/(3.92-4.10).
 4. USE CRIMP DIE CD2052-C TO PRODUCE .161 CUT OFF AND CD2052-E TO PRODUCE .215 CUT OFF.

FINISH CODES:
901 HOT TIN DIP .000020/(0.0005) MIN.



SECTION C-C

MATERIAL NOTES:
1. RED BRASS, ALLOY #C23000;
.010/(0.25) THICK, EXTRA SPRING TEMPER.



DIMENSIONS SHOWN (METRIC) INCH		▽ = 0 ▼ = 0		MFG. SH. REV. LTR. REVISIONS	
UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°		REVISE ONLY ON CAD SYSTEM		F1	
INCH		METRIC		REV'D. AND REDRAW FOR U11047	
3 PLACE	± .010	---	---	10/13/92 RW	
2 PLACE	± .014	± 0.25	---	DATE	
1 PLACE	---	± 0.36	---	10/13/92	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-2282-*	
DRWG. BY: CWF	CHKD. BY: RW	FILE NAME: SD2282X1	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		REV. CP
APP'D. BY: CWF	SCALE: 6:1	DATE: 10/13/92	SIZE: CP		C

2282

D

C

B

A